



ESD Bench Matting - Smooth Finish - Green

Features:

Anti-static matting should be laid out in the workshops or advanced laboratories for microelectronic industries such as electronic semi-conduct devices, electronic computers, electronic communication equipment and integrated circuits etc.

- Great value ESD Bench Matting with grounding cord and two 10mm studs to two corners
- Made from anti-static (conductive) and static-dissipative materials with synthetic rubber
- 3mm thick double-layer structure
- Surface layer is a 1.25mm thick static-dissipative layer
- Middle layer is a 0.5mm conductive layer
- Bottom layer is a 1.25mm thick static-dissipative layer
- Asian origin
- Gray and Blue colours also available





GROUNDING:

Sufficient ground cords should be used to reliably meet EN 61340-5-1 Table 3 less than 1 x 10⁹ ohms for working surfaces. Industry recommendation is that continuous runs of ESD matting should be grounded at 10ft intervals to allow proper charge decay rates. Each individual ESD mat should be grounded with ground snaps located no further than five feet from either end.

CLEANING:

http://www.farnell.com

http://www.newark.com http://www.cpc.co.uk

Please note that contact between the matting surface and any acid or alkali solvent is strictly prohibited (such as Benzene, Alcohol etc), this will result in the antistatic performance wearing away. If cleaning is required, the matting may be wiped with a cloth coated in a neutral solution (such as water).

CUTTING TOLERANCES: Width \pm 6mm, Length \pm 6mm every linear foot of running material.

Disclaimer: This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No license is granted for the use of it other then for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence. SPC Multicomp is the registered trademark of the Group. © Premier Famell plc 2008.





ESD Bench Matting - Smooth Finish - Green

GUIDANCE ON USE:

Matting materials have a tendency to shrink slightly when first unrolled. In applications where length is critical, allow the material to relax for at least 4 hours before cutting to size. Matting should always be trimmed with a sharp knife or razor blade.

RoHS COMPLIANCE:

None of the following materials are intentionally added in manufacturing this product: lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB) or polybrominated diphenyl ethers (PBDE) as outlined in the Directive 2002/95/ EC Article 4.1.

TEST RESULTS:

	Test Method:	Unit:	Value:
Surface Resistance / R _{TG}	SJ/T10694-2004	Ω	$1x10^{6} \le R \le 1x10^{9}$
Bottom Resistance / R_{TT}	SJ/T10694-2004	Ω	$1x10^{6} \le R \le 1x10^{9}$
Volume Resistance	GB/T14437-97	Ω	$1x10^{5} \le R \le 1x10^{8}$
Thickness	YY-1001	mm	Permissable Tolerance +0.1
Temperature Resistance	YY-1001	°C	180 (Instantaneous Temp)
Temperature	N/A	°C	20-26
Relative Humidity	N/A	%	40-65

 R_{TG} is the resistance from one point on the mat's surface to the mat's ground point, and is the fundamental electrical test for a mat. A proper R_{TG} insures that a mat can conduct charge from a point on the surface to the mat ground point. The guideline in ESD STM-4.1 for R_{TG} is 1x10⁶ to 1x10⁹ ohms. ANSI/ESD S-20.20 has an upper limit of <1 x10⁹ ohms.

 $R_{\tau\tau}$ is the resistance from one point on the mat's surface to another point. A proper $R_{\tau\tau}$ insures the consistency of the mat's resistance properties. The ESD STM-4.1 guideline for $R_{\tau\tau}$ is >1x10⁶ ohms.

Straight Earth Lead

Features:

One end supplied with a single ring terminal the other end features a 10mm snap and 2 x 4mm banana sockets.

Material :

- Special conductive wire
- · Each straight cord contains 10 special conductive wires
- Outer covered with Non-Conductive PU
- Length: 10ft
- Diameter of cord: 2.4 mm
- Resistivity : 1M Ohm +/- 10%

Disclaimer: This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No license is granted for the use of it other then for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.

http://www.farnell.com http://www.newark.com http://www.cpc.co.uk





ESD Bench Matting - Smooth Finish - Green

Product Code:	Description:	Size:	Additional Notes:
MC36350	ESD Bench Matting - Smooth Finish Supplied with two studs to two corners and 10ft Straight Earth Lead (10mm stud - ring terminal)	2 x 4'	Green (Ref: 082-0210)

Disclaimer: This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No license is granted for the use of it other then for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the group's liability of death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.



http://www.farnell.com http://www.newark.com http://www.cpc.co.uk