

Screw tap, HSSE M ISO 2 (6H) 15° (right) 371 C

for use in non-ferrous metals

ATORN®



Application

For producing metric threads on CNC or conventional machines in **through holes** in the non-ferrous metals material group.

Version

- structural dimensions in accordance with: DIN 371 = reinforced shank (up to M10), DIN 376 = over-long shank (from M12)

Advantage

- innovative cutting geometry with interrupted thread reduces torque, improves lubricant distribution and ensures extremely good process reliability and chip removal
- specialised application with optimised chip geometry, for use in non-ferrous metals with adhesive or lubricating properties

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	16					18	18	15	18	15	15	13							

Art. No.	13254 100
Type	M MAX Control
Thread type	Metric thread
Thread type x nominal diameter	M10
Pitch	1.5 mm
Hole type	Blind hole ≤ 2.5xD
Cutting material	HSSE
Surface	Uncoated
Lead angle shape	C
Tolerance of screw taps	ISO 2 (6H)
Twist angle	15° (right)
Shaft diameter	10 mm
Application type/machine type	CNC, Conventional
Core hole diameter	8.5 mm
Coolant supply	External
Length	100 mm
Shank square	8 mm
Cutting speed (steel 1000) suitability	3
Cutting speed (steel 1300) suitability	3
Overall stainless steel suitability	3
fitness not iron total	1
fitness Titan/Nickel/Super total	3
Cutting speed (cast) suitability	3
Cutting speed (hard 55) suitability	3
Cutting speed (hard 65) suitability	3
DIN	371

EAN-Code

4050293189629