

Pneumatic straight grinder SRH 8-20/2

With lever valve



Application:

For coarse work with milling pins of head diameter up to 12 mm.

Execution:

- Rear air exhaust

Advantage:

- Increased wear resistance.

Delivery:

Includes collet chuck ZG 7/6 mm and collet chuck key size 11 + 14; in box



Art. no.	75036 095
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150020800
Model	SRH 8-20/2
Valve design	Lever valve
Max. idle speed	20000 rpm
Power output	300 W
Air consumption	500 l/min
Connection thread	R 1/8 inch
Inner hose diameter	7 mm
Length	218 mm
Diameter of housing	41 mm
Max. clamping diameter	8 mm
Collet chuck diameter	6 mm
Suitable for max. sanding block diameter	24 mm
Max. HM rotating milling cutter diameter	12 mm
Weight	0.62 kg
Gross Weight	1.270 kg
Product Group	748