


# AC5222



## AS-Interface ClassicLine module with quick mounting technology

ClassicLine 2AI C IP67



### Electrical data

Operating voltage [V]	26.5...31.6 DC; ("supply class 2" to cULus)
Max. current consumption from AS-i [mA]	250
Reverse polarity protection	yes

### Inputs / outputs

Number of inputs and outputs	Number of analogue inputs: 2
------------------------------	------------------------------

### Inputs

Number of analogue inputs	2; (Anschluss von 2- und 3-Draht-Sensoren)
Sensor supply of the inputs	AS-i
Analogue input (current) [mA]	4...20
Max. voltage drop across load for nominal voltage [V]	10
Analogue inputs protected against short circuits	yes
Resolution of analogue input	12 bit

### Operating conditions

Ambient temperature [°C]	-25...70
Protection	IP 67

### Tests / approvals

EMC	EN 50295
MTTF [years]	174

# AC5222



## AS-Interface ClassicLine module with quick mounting technology

ClassicLine 2AI C IP67

AS-i classification				
AS-i version		2.11 + 3.0		
AS-i addressing		addressing socket		
Extended addressing mode possible		no		
AS-i profile		S-7.3.D		
AS-i I/O configuration	[hex]	7		
AS-i ID code	[hex]	3.D		
AS-i certificate pending		yes		
Mechanical data				
Weight	[g]	176		
Type of mounting		AS-i flat cables directly connectable		
Materials		PA; piercing contacts: CuSn6 nickel-plated and tin-plated		
Displays / operating elements				
Display	operation	LED, green Voltage AS-i		
	errors	LED, red		
	function	LED, yellow channels AI1, AI2		
Accessories				
Accessories (supplied)		lower part		
Accessories (optional)		Protective cap: M12, E73004		
Remarks				
Remarks	When the actuators are supplied from AS-i the load must not exceed a maximum of 200 mA.			
	There is an electrical connection between the sensor and AS-i.			
	The module is exclusively supplied via the yellow AS-i cable.			
Pack quantity	1 pcs.			
Electrical connection				
quick mounting technology for AS-i flat cable: ; three orientations possible				
1	Sensor supply +24V			
2	analogue input AI +			
3	Sensor supply 0V / analogue input AI-			
5	functional earth			
Connector: M12				
