



SAFETY DATA SHEET
QUICK DRY RED OXIDE PRIMER

Page: 1

Compilation date: 21/07/2015

Revision date: 26/02/2018

Revision No: 2

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: QUICK DRY RED OXIDE PRIMER

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: Rustins Ltd
Waterloo Road
Cricklewood
London
NW2 7TX
United Kingdom

Tel: +44 (0)208 450 4666

Fax: +44 (0)208 452 2008

Email: rustins@rustins.co.uk

1.4. Emergency telephone number

Emergency tel: .+44(0)2084504666 (Office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: -: EUH208

Most important adverse effects: Contains 5-chloro-2-methyl-2h-isothiazol-3-one(acticide fsn). May produce an allergic reaction.

2.2. Label elements

Label elements:

Hazard statements: EUH208: Contains 5-chloro-2-methyl-2h-isothiazol-3-one(acticide fsn). May produce an allergic reaction.

Precautionary statements: P102: Keep out of reach of children.

P301+312: IF SWALLOWED: Call a doctor if you feel unwell.

P262: Do not get in eyes, on skin, or on clothing.

P280: Wear protective gloves and eye protection.

P302+350: IF ON SKIN: Gently wash with plenty of soap and water.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

[cont...]

SAFETY DATA SHEET
QUICK DRY RED OXIDE PRIMER

Page: 2

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

5-CHLORO-2-METHYL-2H-ISOTHIAZOL-3-ONE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
-	55965-84-9	-	Skin Corr. 1B: H314; Skin Sens. 1: H317	0.200%

BYK- 420

-	-	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319; Repr. 1B: H360D; STOT SE 3: H335	0.100%
---	---	---	---	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water. Do not induce vomiting. If unconscious and breathing is OK, place in the recovery position. Consult a doctor.

Inhalation: Not applicable.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Show this safety data sheet to the doctor in attendance.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

[cont...]

SAFETY DATA SHEET
QUICK DRY RED OXIDE PRIMER

Page: 3

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Turn leaking containers leak-side up to prevent the escape of liquid. Do not attempt to take action without suitable protective clothing - see section 8 of SDS. Mechanically ventilate the spillage area whilst avoiding the formation of explosive concentrations - see section 9 of SDS. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Ensure a retention tank is installed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure a retention tank is installed.

Respiratory protection: Respiratory protection not required. Self-contained breathing apparatus must be available in case of emergency.

[cont...]

SAFETY DATA SHEET
QUICK DRY RED OXIDE PRIMER

Page: 4

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Red-brown

Odour: Barely perceptible odour

Evaporation rate: No data available.

Oxidising: No data available.

Solubility in water: Miscible

Viscosity: Viscous

Boiling point/range°C: No data available.

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: >93

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available.

Vapour pressure: No data available.

Relative density: 1.07

pH: 7

VOC g/l: No data available.

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Heat. Direct sunlight.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

[cont...]

SAFETY DATA SHEET
QUICK DRY RED OXIDE PRIMER

Page: 5

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: No data available.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: No data available.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: No data available.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: NOT CLASSIFIED

14.2. UN proper shipping name

[cont...]

SAFETY DATA SHEET
QUICK DRY RED OXIDE PRIMER

Page: 6

14.3. Transport hazard class(es)

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.

H314: Causes severe skin burns and eye damage.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

H360D: May damage the unborn child.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.