



SIRIUS SOFT STARTER, VALUES WITH 500 V, 40 DEG., STANDARD: 36A, 22KW, INSIDE-DELTA CIRCUIT 3: 62A, 37KW, 400-600 V AC, 230 V AC, CAGE CLAMP TERMINALS

General technical data:

| | | |
|---|--|--------|
| product brand name | | SIRIUS |
| Product feature | | |
| <ul style="list-style-type: none"> integrated bypass contact system | | Yes |
| <ul style="list-style-type: none"> Thyristors | | Yes |
| Product function | | |
| <ul style="list-style-type: none"> Intrinsic device protection | | Yes |
| <ul style="list-style-type: none"> motor overload protection | | Yes |
| <ul style="list-style-type: none"> Evaluation of thermistor motor protection | | Yes |
| <ul style="list-style-type: none"> External reset | | Yes |
| <ul style="list-style-type: none"> Adjustable current limitation | | Yes |
| <ul style="list-style-type: none"> inside-delta circuit | | Yes |
| Product component Motor brake output | | Yes |
| Equipment marking acc. to DIN EN 61346-2 | | Q |
| Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750 | | G |

Power Electronics:

| | | |
|---|---|---|
| Product designation | | soft starters for high feature applications |
| Operating current | | |
| <ul style="list-style-type: none"> at 40 °C Rated value | A | 36 |
| <ul style="list-style-type: none"> at 50 °C Rated value | A | 32 |
| <ul style="list-style-type: none"> at 60 °C Rated value | A | 29 |
| Operating current for three-phase motors at 3-phase root switching | | |
| <ul style="list-style-type: none"> at 40 °C Rated value | A | 62 |

| | | |
|---|----|-------------|
| • at 50 °C Rated value | A | 55 |
| • at 60 °C Rated value | A | 50 |
| Mechanical power output for three-phase motors | | |
| • at 400 V | | |
| — at standard circuit at 40 °C Rated value | W | 18 500 |
| — at 3-phase root switching at 40 °C Rated value | W | 30 000 |
| • at 500 V | | |
| — at standard circuit at 40 °C Rated value | W | 22 000 |
| — at 3-phase root switching at 40 °C Rated value | W | 37 000 |
| Operating frequency Rated value | Hz | 50 ... 60 |
| Relative negative tolerance of the operating frequency | % | -10 |
| Relative positive tolerance of the operating frequency | % | 10 |
| Operating voltage at standard circuit Rated value | V | 400 ... 600 |
| Relative negative tolerance of the operating voltage at standard circuit | % | -15 |
| Relative positive tolerance of the operating voltage at standard circuit | % | 10 |
| Operating voltage at 3-phase root switching Rated value | V | 400 ... 600 |
| Relative negative tolerance of the operating voltage at 3-phase root switching | % | -15 |
| Relative positive tolerance of the operating voltage at 3-phase root switching | % | 10 |
| Minimum load in % of I_M | % | 8 |
| Adjustable motor current for motor overload protection minimum rated value | A | 7 |
| Continuous operating current in % of I_e at 40 °C | % | 115 |
| Active power loss at operating current at 40 °C during operation typical | W | 10 |

Control electronics:

| | | |
|--|----|-----|
| Type of voltage of the control supply voltage | | AC |
| Control supply voltage frequency 1 Rated value | Hz | 50 |
| Control supply voltage frequency 2 Rated value | Hz | 60 |
| Relative negative tolerance of the control supply voltage frequency | % | -10 |
| Relative positive tolerance of the control supply voltage frequency | % | 10 |
| Control supply voltage 1 with AC | | |
| • at 50 Hz Rated value | V | 230 |
| • at 60 Hz Rated value | V | 230 |

| | | |
|--|---|---------|
| Relative negative tolerance of the control supply voltage with AC at 60 Hz | % | -15 |
| Relative positive tolerance of the control supply voltage with AC at 60 Hz | % | 10 |
| Display version for fault signal | | Display |

Mechanical data:

| | | |
|---|----|---|
| Width | mm | 170 |
| Height | mm | 192 |
| Depth | mm | 270 |
| Mounting type | | screw fixing |
| mounting position | | bei senkrechter Montageebene +/-90° drehbar, bei senkrechter Montageebene +/- 22,5° nach vorne und hinten kippbar |
| Required spacing with side-by-side mounting | | |
| • upwards | mm | 100 |
| • at the side | mm | 5 |
| • downwards | mm | 75 |
| Installation altitude at height above sea level | m | 5 000 |
| Cable length maximum | m | 500 |
| Number of poles for main current circuit | | 3 |

Connections/ Terminals:

| | | |
|---|--|----------------------------|
| Type of electrical connection | | |
| • for main current circuit | | box terminals |
| • for auxiliary and control current circuit | | spring-loaded terminals |
| Number of NC contacts for auxiliary contacts | | 0 |
| Number of NO contacts for auxiliary contacts | | 3 |
| Number of CO contacts for auxiliary contacts | | 1 |
| Type of connectable conductor cross-section for main contacts for box terminal using the front clamping point | | |
| • solid | | 2.5 ... 16 mm ² |
| • finely stranded with core end processing | | 2.5 ... 35 mm ² |
| • finely stranded without core end processing | | 4 ... 50 mm ² |
| • stranded | | 4 ... 70 mm ² |
| Type of connectable conductor cross-section for main contacts for box terminal using the back clamping point | | |
| • solid | | 2,5 ... 16 mm ² |
| • finely stranded with core end processing | | 2.5 ... 50 mm ² |
| • finely stranded without core end processing | | 10 ... 50 mm ² |
| • stranded | | 10 ... 70 mm ² |

| | | |
|--|--|--|
| Type of connectable conductor cross-section for main contacts for box terminal using both clamping points | | |
| <ul style="list-style-type: none"> • solid • finely stranded with core end processing • finely stranded without core end processing • stranded | | 2x (2.5 ... 16 mm ²) 2x (2.5 ... 35 mm ²) 2x (4 ... 35 mm ²) 2x (4 ... 50 mm ²) |
| Type of connectable conductor cross-section for AWG conductors for main contacts for box terminal | | |
| <ul style="list-style-type: none"> • using the back clamping point • using the front clamping point • using both clamping points | | 10 ... 2/0 10 ... 2/0 2x (10 ... 1/0) |
| Type of connectable conductor cross-section for auxiliary contacts | | |
| <ul style="list-style-type: none"> • solid • finely stranded with core end processing | | 2x (0.25 ... 1.5 mm ²) 2x (0.25 ... 1.5 mm ²) |
| Type of connectable conductor cross-section for AWG conductors | | |
| <ul style="list-style-type: none"> • for auxiliary contacts | | 2x (24 ... 16) |

Ambient conditions:

| | | |
|--|----|-------------------|
| Ambient temperature | | |
| <ul style="list-style-type: none"> • during operation • during storage | °C | 60 -25 ... +80 |
| Derating temperature | °C | 40 |
| Protection class IP | | IP00 |

Certificates/ approvals:

| | | |
|--------------------------|-----|---------------------------|
| General Product Approval | EMC | Declaration of Conformity |
|--------------------------|-----|---------------------------|



| | |
|-------------------|-------------------|
| Test Certificates | Shipping Approval |
|-------------------|-------------------|

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)



| | |
|-------------------|-------|
| Shipping Approval | other |
|-------------------|-------|



[Environmental Confirmations](#)

UL/CSA ratings:

| | | |
|--|-----------|-------------|
| <p>yielded mechanical performance [hp] for three-phase AC motor</p> <ul style="list-style-type: none"> at 460/480 V <ul style="list-style-type: none"> at standard circuit at 50 °C Rated value at 3-phase root switching at 50 °C Rated value at 575/600 V <ul style="list-style-type: none"> at standard circuit at 50 °C Rated value at 3-phase root switching at 50 °C Rated value | metric hp | 20 |
| | metric hp | 40 |
| | metric hp | 25 |
| | metric hp | 50 |
| Contact rating of the auxiliary contacts acc. to UL | | B300 / R300 |

Further information




Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)
<http://www.siemens.com/industrymall>

Cax online generator
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW44233BC45>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<http://support.automation.siemens.com/WW/view/en/3RW44233BC45/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RW44233BC45&lang=en>



last modified:

15.01.2015