



SIMATIC DP, 1 ELECTRON. MODULE FOR ET 200S, 8 DI SOURCE INPUT 24V DC, 15 MM WIDTH, 1 PIECE PER PACKAGING UNIT

Supply voltage

Rated value (DC)	Yes; From power module
<ul style="list-style-type: none"> • 24 V DC 	
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes

Input current

from supply voltage L+, max.	Dependent on encoder
------------------------------	----------------------

Power losses

Power loss, typ.	1.2 W
------------------	-------

Digital inputs

Number of digital inputs	8
Input characteristic curve in accordance with IEC 61131, type 1	Yes

Input voltage	
<ul style="list-style-type: none"> • Type of input voltage • Rated value (DC) • for signal "0" • for signal "1" 	DC 24 V -5 to +30V -15 to -30 V

Input current	
<ul style="list-style-type: none"> • for signal "1", typ. 	6 mA; at 24 V

Input delay (for rated value of input voltage)	
for standard inputs	
— Parameterizable	No

— at "0" to "1", min.	2 ms
— at "0" to "1", max.	4.5 ms
— at "1" to "0", min.	2 ms
— at "1" to "0", max.	4.5 ms
Cable length	
• shielded, max.	1 000 m
• Unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— Permissible quiescent current (2-wire sensor), max.	1.5 mA
Isochronous mode	
Isochronous operation (application synchronized up to terminal)	Yes
Diagnostic messages	
• Diagnostic functions	No
Diagnostics indication LED	
• Group error SF (red)	No
• Status indicator digital input (green)	Yes; per channel
Parameter	
Remark	3 byte
Galvanic isolation	
Galvanic isolation digital inputs	
• between the channels	No
• between the channels and the backplane bus	Yes
Permissible potential difference	
between different circuits	75V DC/60V AC
Isolation	
Isolation checked with	500 V DC
Dimensions	
Width	15 mm
Height	81 mm
Depth	52 mm
Weights	
Weight, approx.	35 g
last modified:	12.03.2015