

Product type designation



CP 5614 A3

COMMUNICATION PROCESSOR CP 5614 A3, PCI-CARD (32BIT; 3.3/5V; 33/66MHZ); WITH MASTER UND SLAVE INTERFACE FOR CONNECT. TO PROFIBUS; INCL. CONFIGURATION TOOL AND DP-BASE SOFTWARE: DP-RAM INTERFACE FOR DP-MASTER; INCL. PG- AND FDL-PROTOCOL; SINGLE LICENSE FOR 1 INSTALLAT. RUNTIME SOFTWARE, CLASS A; SW + ELECTR. MANUALS ON DVD 2-LANGUAGES (G,E); SUPPORT FOR OPERATING SYSTEM SEE SIMATIC NET SOFTWARE V12

Transmission rate

Transfer rate

- | | |
|---|--------------------------|
| • at the 1st interface / acc. to PROFIBUS | 9.6 kbit/s ... 12 Mbit/s |
| • at the 2nd interface / acc. to PROFIBUS | 9.6 kbit/s ... 12 Mbit/s |

Interfaces

Number of electrical connections

- | | |
|---|---|
| • at the 1st interface / acc. to PROFIBUS | 1 |
| • at the 2nd interface / acc. to PROFIBUS | 1 |

Type of electrical connection

- | | |
|---|-----------------------------|
| • at the 1st interface / acc. to PROFIBUS | 9-pin Sub-D socket (RS 485) |
| • at the 2nd interface / acc. to PROFIBUS | 9-pin Sub-D socket (RS 485) |

Supply voltage, current consumption, power loss

Type of voltage / of the supply voltage

DC

Supply voltage

- | | |
|--------------------------|-------|
| • 1 / from backplane bus | 3.3 V |
| • 2 / from backplane bus | 12 V |

Relative symmetrical tolerance / for DC

- | | |
|------------|-----|
| • at 3.3 V | 9 % |
| • at 12 V | 8 % |

Consumed current

- | | |
|---|--------|
| • 1 / from backplane bus / for DC / maximum | 0.15 A |
| • 2 / from backplane bus / for DC / maximum | 0.3 A |

Active power loss

4 W

Permitted ambient conditions	
Ambient temperature	
<ul style="list-style-type: none"> during operation 	5 ... 55 °C
<ul style="list-style-type: none"> during storage 	-20 ... +60 °C
<ul style="list-style-type: none"> during transport 	-20 ... +60 °C
Relative humidity / at 25 °C / without condensation / during operation / maximum	85 %
Protection class IP	IP00

Design, dimensions and weight	
Module format	PCI
Width	18 mm
Height	107 mm
Depth	125 mm
Net weight	0.118 kg
Number of plug-in cards of same design / plug-in / per PC station	4
Number of units / Note	-

Performance data

Performance data / open communication	
Software / for open communication / by means of SEND/RECEIVE / required	FDL driver included in scope of delivery of the CP
Number of possible connections / for open communication / by means of SEND/RECEIVE / maximum	80

Performance data / PROFIBUS DP

Software / for DP master function / required	No
Service / as DP master	
<ul style="list-style-type: none"> DPV0 	Yes
<ul style="list-style-type: none"> DPV1 	Yes
<ul style="list-style-type: none"> DPV2 	Yes
Number of DP slaves / on DP master / usable	124
Amount of data	
<ul style="list-style-type: none"> of the address area of the inputs / as DP master / total 	30256 byte
<ul style="list-style-type: none"> of the address area of the outputs / as DP master / total 	30256 byte
<ul style="list-style-type: none"> of the address area of the inputs / per DP slave 	244 byte
<ul style="list-style-type: none"> of the address area of the outputs / per DP slave 	244 byte
<ul style="list-style-type: none"> of the address area of the diagnostic data / per DP slave 	244 byte
Software / for DP slave function / required	No

Service / as DP slave	
• DPV0	Yes
• DPV1	Yes
Amount of data	
• of the address area of the inputs / as DP slave / total	244 byte
• of the address area of the outputs / as DP slave / total	244 byte

Performance data / S7 communication

Software / for S7 communication / required	Yes, HARDNET-PB S7 (S7-5613)
Number of possible connections / for S7/PG communication / maximum	50

Performance data / multi-protocol mode

Number of active connections / with multi-protocol mode	50
Number of configurable connections / per PC station	207

Product functions / management, configuration

Configuration software / required	Included in scope of supply
-----------------------------------	-----------------------------

Product functions / Diagnosis

Product function	
• Port diagnostics	Yes

Standards, specifications, approvals

Standard	
• for EMC	89/336/EEC
• for safety / from CSA and UL	CAN/CSA C22.2 & UL 60950-1, UL 1950
• for emitted interference	EN 61000-6-3
• for interference immunity	EN 61000-6-2
Certificate of suitability	
• CE marking	Yes
• C-Tick	Yes

Further Information / Internet Links

Internet-Link	
• to website: Selector SIMATIC NET SELECTION TOOL	http://www.siemens.com/snst
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	http://www.siemens.com/industrial-controls/mall
• to website: Information and Download Center	http://www.siemens.com/automation/net/catalog
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx Download Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

09.03.2015