


# BZV03/Z0000/05 Datasheet

**Product Name // Vertical Power Entry Module 78.7mm C14  
Cold Condition Inlet (PX0575) 6.3mm Tab Termination  
Unfiltered 2 x FX0359 Fuseholders Double Contact Switch**

[View Product Page](#)


Panel Thickness: 10, 15, 20, 30mm.  
BZV03, BZV04/xxxx/xx A = 32.5 With Filter  
38.0 Without Filter  
BZV05, BZV06/xxxx/xx A = 39.0

## // Product Description:

- ⊗ Vertical Power Entry Module 50.8mm/78.7mm
- ⊗ C14 Cold Condition Inlet (PX0575)
- ⊗ Choice of Termination depending on part code:
- ⊗ Part codes prefixed BZV03: 6.3mm Tab
- ⊗ Part codes prefixed BZV04: 2.8mm Tab
- ⊗ Choice of mains filter depending on part code:
- ⊗ Part codes containing /Z0000 are unfiltered
- ⊗ Choice of mains filter options (part codes containing codes starting /A)
- ⊗ Choice of many other options as specified by individual part code, including fuseholders, voltage selectors, indicators, illuminated switches, switch markings, etc
- ⊗ Also available in C16 Hot Condition Inlet (PX0595) versions in both Terminations (6.3mm Tab part code BZV05, 2.8mm Tab part code BZV06), Unfiltered only

## // General Information:

Product Configurator:	No
Product Display Title:	Vertical Power Entry Module 50.8mm/78.7mm
Product Family:	IEC Connectors
Product Series:	Power Entry Modules
Pdfbuilder Enabled:	Yes
Function:	C14 Inlets
iec Connector Mates With:	PX0575
iec Vertical Module Height:	78.7mm
Inlet Type:	C14 Cold Condition Inlet
Product Technical Image:	/b/z/bzv03z000007_diagram.jpg
Switch Type:	Double Contact
Package Id:	564

## // Electrical Specifications:

Current Max:	10A
Filter Type:	Unfiltered
iec Connector Components:	None
iec Filter Options:	Unfiltered
Number Of Fuseholders:	2 x FX0359 Fuseholders
Voltage Max:	250V

### // Product PDF Links

[Power Entry Modules product data](#)

### // Product 3D CAD Model Links

[BZV03/Z0000/053D CAD Model](#)