



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Wave solder capable to 240°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #1-178313-2
DYNAMIC 3100 HDR ASSY







TE Part #1318758-1
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #172035-1
MIC CAP 9P V



TE Part #5178405-1
040 SEALED PAIR MATE 120P CAP
ASSY



Documents

Product Drawings

MIC CAP 11P V

Japanese

CAD Files

Customer View Model

[ENG_CVM_172034-1_F2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_172034-1_F2.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_172034-1_F2.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Multi-Interlock Mark II Connector for Wire to Board Termination

English

Product Specification

English

Multi-Interlock Mark II Connector for Printed Circuit Board

Japanese

Product Specification

Japanese

Instruction Sheets

Multi Interlock Connector Mark II

English

Customer Manual (non U.S.)

English

Customer Manual (non U.S.)

Japanese



Multi Interlock Connector Wire to PCB Type

Japanese

[Agency Approvals](#)

[Agency Approval Document](#)

English