

Einsatzempfehlung

Material	Stahl N/mm ²			Rostfreie Stähle		Guss		NE-Metalle			Superleg.		Stahl gehärtet		
Zugfestigkeit	<500	<800	<1200 (<HRC38)	<1600 (<HRC48)	<800	<1200	GG	GGG	Al Knetleg.	Al Si<10%	Cu, Ms	Ti/Ni/Co <900	900-1500	HRC 48-57	HRC 58-63
40 00 861 202 - Vc (m/min)	60-80	50-70	30-40		20-30	10-20	80-90	70-80	200	120-150	50-180	12-15	8-12		
40 00 861 252 - Vc (m/min)	70-100	60-90	50-70		25-40	15-20	120-160	95-120	200	140-170	45-210	15-25	10-20		
Kühlung	Emulsion	Emulsion/Öl	Emulsion/Öl		Öl	Emulsion/öl	Emulsion	Emulsion	Emulsion	Emulsion	Emulsion/Öl	Öl	Emulsion/Öl		