

Twist drill type N HSS, steam-treated

for universal use up to 1000 N/mm²

ATORN®



Application

Standard geometry for universal use up to 1000 N/mm².

Version

- Twist drill with universal standard geometry

Advantage

- excellent all-round properties and precise cutting pattern
- universal use: minimises tool costs and improves flexibility
- Steam treatment ensures favourable adherence of coolant

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas- tics	Graphite G(C)FK	GG(G) GjMW	Titan- alloy	Nickel- alloy	Super- alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	30	20		10		50	45	40	35	40	30	20	10	25					

Art. No.	11070 176
Cutting material	HSS
Surface	Vaporised
Type	N
Angle of the tip	118 Degree
Tool holding device	Morse taper shank
Cutting edge diameter	15.25 mm
Chip flute length	120 mm
Length	218 mm
Morse taper size	MK 2
f steel 700	0.27 mm/U
DIN	345

EAN-Code

4050293033885