

Horizontal quick-action clamp

With open clamping arm and horizontal base



Application:


For quick clamping of workpieces.

Version:

- Galvanised and passivated
- Ergonomic, oil-resistant handle with large hand rest and soft components.
- Case-hardened and lubricated bearing bushes

Delivery:

With thrust bolt and protective cap



Art. no.	26215 020
Size	2
Hole distance	26 mm
Min./max. distance between stop and centre of drill	19.5-29.5 mm
Bore diameter	5.6 mm
Clamping height	24 mm
Retaining force	1000 N
Max. tensile force	1200 N
Height	45 mm
Length 2	162 mm
Thumbscrew size	M6 x 35 mm

EAN-Code

4020772093020