

## Drill quick-action clamping vices

With integrated quick adjustment

**ATORN**<sup>®</sup>

### Application

For quick and safe clamping, in particular for workpiece series machining; can be used with guide rails; clamping on base and side; also suited for light milling tasks.

### Version

- Special cast iron body
- Flat and sturdy design
- max. Clamping force 10 kN
- Positive locking engagement

### Advantage

- Quick jaw adjustment and clamping with just one lever
- one-handed operation
- Large clamping range

### Delivery

1 pc. Drill quick-release vice incl. fastening material



<b>Art. no.</b>	<b>28671 110</b>
<b>Jaws width</b>	110 mm
<b>Clamping width</b>	130 mm
<b>Jaws height</b>	32 mm
<b>Jaws thickness</b>	12 mm
<b>Body length</b>	280 mm
<b>Max. length</b>	465 mm
<b>Body width</b>	112 mm
<b>Clamp in height</b>	50 mm
<b>Height</b>	82 mm
<b>Weight</b>	12.5 kg

### EAN-Code

4050293150292