


BZV01/A0620/11 Datasheet

**Product Name // Vertical Power Entry Module 72.3mm C14
Cold Condition Inlet Integral Single Fused (PF0011) 6.3mm
Tab Termination A0620 Filter (6A PS21/A L/C v2) Double
Contact Illuminated Switch Red**

[View Product Page](#)


// Product Description:

- ⊞ Vertical Power Entry Module 58.9mm/72.3mm
- ⊞ C14 Cold Condition Inlet with integral fuseholder(s) depending on part code:
- ⊞ Part codes prefixed BZV01, BZV02: PF0011 Single Fused Inlet
- ⊞ Part codes prefixed BZV15, BZV16: PF0033 Twin Fused Inlet
- ⊞ Choice of Termination depending on part code:
- ⊞ Part codes prefixed BZV01, BZV15: 6.3mm Tab
- ⊞ Part codes prefixed BZV02, BZV16: 2.8mm Tab
- ⊞ Choice of mains filter depending on part code:
- ⊞ Part codes containing /Z0000 are unfiltered
- ⊞ Choice of mains filter options (part codes containing codes starting /A)
- ⊞ Choice of many other options as specified by individual part code, including indicators, illuminated switches, switch markings, etc

// General Information:

Product Configurator:	No
Product Display Title:	Vertical Power Entry Module 58.9mm/72.3mm
Product Family:	IEC Connectors
Product Series:	Power Entry Modules
Pdfbuilder Enabled:	Yes
Function:	C14 Inlets
Iec Connector Mates With:	PF0011
Iec Vertical Module Height:	72.3mm
Inlet Type:	C14 Cold Condition Inlet
Product Technical Image:	/b/z/bzv01z000010_diagram.jpg
Switch Type:	Double Contact Illuminated
Package Id:	564

// Electrical Specifications:

Current Max:	6A
Filter Type:	6A PS21/A L/C v2
Fuseholder Inlet Type:	Integral Single Fused
Iec Connector Components:	None
Iec Filter Options:	A0620
Iec Neon Colour:	Red
Voltage Max:	250V

// Product PDF Links

[Power Entry Modules product data](#)

// Product 3D CAD Model Links

[BZV01/A0620/113D CAD Model](#)