



**Part no.: 50130599**  
**MD 7XXP-11-88IO3-K100**  
**Distribution box**



Figure can vary

## Contents

- Technical data
- Electrical connection
- Circuit diagrams
- Operation and display
- Accessories

## Technical data

<b>Electrical data</b>	
Switching signal	PNP
<b>Performance data</b>	
Total current	10 A
<b>Input data logic</b>	
Nominal input voltage $U_N$	24 V DC
<b>Connection</b>	
<b>Master connection</b>	
Type of connection	Cable
Function	Connection to the control
Cable length	10,000 mm
<b>Cable properties</b>	
Number of conductors	3 Piece(s)
Wire cross section	2 x 0.75 mm <sup>2</sup> 8 x 0.34 mm <sup>2</sup>
AWG	22
Sheathing color	Gray
Shielded	No
Silicone-free	No
Cable design	Connection cable (open on one end)
Cable diameter (external)	8.6 mm
Cable length	10,000 mm
Sheathing material	PUR
Wire insulation	PVC
Suitability for drag chains	Yes
Traverse rate	Max. 2m/s with horiz. traverse path of 5m and max. acceleration of 10m/s <sup>2</sup>
Resistance of the outer sheathing	Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2
<b>Distribution box connections</b>	
Number of connections	8 Piece(s)
Thread size	M8
No. of pins	3 -pin
Encoding	A-coded
Type	Female
Material	Plastic
Material of O-ring seal	TPU
Material of contacts	Gold-plated
Operating current per contact	2 A
<b>Mechanical data</b>	
Design	Cubic
Dimension (W x H x L)	30 mm x 35 mm x 132 mm
Housing material	Plastic
Net weight	1,184 g
Screw tightening torque	0 N·m
Bending cycles	2,000,000 Piece(s)

## Part no.: 50130599 – MD 7XXP-11-88IO3-K100 – Distribution box

Bending radius, flexible laying, min.	Min. 12 x cable diameter
---------------------------------------	--------------------------

### Operation and display

Type of display	LED
-----------------	-----

### Environmental data

Ambient temperature, operation	-5 ... 70 °C
--------------------------------	--------------

### Certifications


Degree of protection	IP 65 IP 67
Certifications	c UL US

### Classification

Customs tariff number	85444290
eCl@ss 8.0	27279219
eCl@ss 9.0	27440108
ETIM 5.0	EC002585
ETIM 6.0	EC002585


## Electrical connection

Connection 1	
Type of connection	Cable
Number of conductors	3 -wire



Conductor color	Conductor assignment
Brown	+
Blue	-
White	S1

## Circuit diagrams




## Operation and display

### LEDs


LED	Display	Meaning
1	Green, continuous light	Operating voltage applied
2	Yellow, continuous light	Signal 1
3	White, continuous light	Signal 2

## Accessories

### Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50134904	KDS U-M8-4A-M8-3A-P1-000	Adapter	Connection 1: Connector, M8, Axial, Female, 4 -pin Connection 2: Connector, M8, Axial, Male, 3 -pin

## General

	Part no.	Designation	Article	Description
	50134479	CAP M8K-Set	Connection cap	Type: Cap for free sockets Thread size: M8 Material: Plastic

### Note

A list with all available accessories can be found on the Leuze electronic website in the Download tab of the article detailed page.