

### Product type designation

Product description

### IE TP Cord RJ45/RJ45, 4x2

Patch cable, preferred length, preassembled with two RJ45 connectors (10/100/1000/10000MB)

SIMATIC NET, IND. ETHERNET TP CORD RJ45/RJ45, CAT 6A, TP CABLE 4X2, PREASSEMBLED W/ 2 RJ45 CONNECTORS,LENGTH 3M



Suitability for use	Easy connection of data terminals to the IE FC cabling system
Cable designation	LI 02YSCH 4x2x0,15 PIMF GN FRNC
Cable length	3 m

### Electrical data

Damping ratio per length	
<ul style="list-style-type: none"> <li>• at 10 MHz / maximum</li> <li>• at 100 MHz / maximum</li> <li>• at 300 MHz / maximum</li> <li>• at 600 MHz / maximum</li> </ul>	<p>0.086 dB/m</p> <p>0.28 dB/m</p> <p>0.501 dB/m</p> <p>0.735 dB/m</p>
Impedance	
<ul style="list-style-type: none"> <li>• at 1 MHz ... 100 MHz</li> <li>• at 10 MHz ... 600 MHz</li> </ul>	<p>100 Ω</p> <p>100 Ω</p>
Relative symmetrical tolerance	
<ul style="list-style-type: none"> <li>• of the characteristic impedance at 1 MHz ... 100 MHz</li> <li>• of the characteristic impedance at 10 MHz ... 600 MHz</li> </ul>	<p>15 %</p> <p>10 %</p>
Transfer impedance per length / at 10 MHz	10 mΩ/m
Loop resistance per length / maximum	290 mΩ/m
NVP value in percent	80 %

### Mechanical data

Number of electrical cores	8
----------------------------	---

Design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires
Core diameter <ul style="list-style-type: none"> <li>• of AWG26 core</li> </ul>	0.5 mm
Outer diameter <ul style="list-style-type: none"> <li>• of inner conductor</li> <li>• of the wire insulation</li> <li>• of cable sheath</li> </ul>	0.5 mm 1 mm 6.2 mm
Symmetrical tolerance of the outer diameter / of cable sheath	0.3 mm
Material <ul style="list-style-type: none"> <li>• of the wire insulation</li> <li>• of cable sheath</li> </ul>	PE FRNC
Color <ul style="list-style-type: none"> <li>• of the insulation of data wires</li> <li>• of cable sheath</li> </ul>	white/blue, white/orange, white/green, white/brown green
Bending radius <ul style="list-style-type: none"> <li>• with single bend / minimum permissible</li> <li>• with multiple bends / minimum permissible</li> </ul>	31 mm 43.5 mm
Weight per length	50 kg/km

#### Permitted ambient conditions

Ambient temperature <ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> <li>• during transport</li> <li>• during installation</li> <li>• Note</li> </ul>	-25 ... +80 °C -25 ... +80 °C -25 ... +80 °C -25 ... +80 °C in fixed installation -40°C to 80°C
Burning behavior	flame resistant according to IEC 60332-1
Chemical resistance <ul style="list-style-type: none"> <li>• to mineral oil</li> <li>• to grease</li> </ul>	oil resistant according to IEC 60811-2-1 (4 h / 70°C) Conditional resistance
Protection class IP	IP20

#### Product properties, functions, components / general

Product property <ul style="list-style-type: none"> <li>• halogen-free</li> <li>• silicon-free</li> </ul>	Yes Yes
---	------------

#### Standards, specifications, approvals

Certificate of suitability <ul style="list-style-type: none"> <li>• UL approval</li> </ul>	Yes
Standard for structured cabling	Cat6A
Marine classification association	

- American Bureau of Shipping Europe Ltd. (ABS)
- Bureau Veritas (BV)
- Det Norske Veritas (DNV)
- Germanische Lloyd (GL)
- Lloyds Register of Shipping (LRS)
- Nippon Kaiji Kyokai (NK)
- Polski Rejestr Statkow (PRS)

No  
No  
No  
No  
No  
No  
No

## Further Information / Internet Links

### Internet-Link

- to website: Selector SIMATIC NET SELECTION TOOL
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/snst>  
  
<http://www.siemens.com/simatic-net>  
<https://mall.industry.siemens.com>  
<http://www.siemens.com/automation/net/catalog>  
<http://automation.siemens.com/bilddb>  
<http://www.siemens.com/cax>  
<https://support.industry.siemens.com>

**last modified:**

12.03.2015