

Automotive Relays

CA RELAYS


Product Catalog

IN Your Future





Small Size, Light Weight Automotive Power Relays




FEATURES

- Small size and light weight
- Since the terminal arrangement complies with JIS
- Low operating power (1.4 W) type is available (1 Form A, 1 Form B).

TYPICAL APPLICATIONS


- Motorcycles and automobiles
 Motorcycle cell motors, car air conditioners, halogen lamps, etc.
- Agricultural equipment
- Battery equipped devices such as conveyance vehicles

ORDERING INFORMATION (PART NO. : Ordering part number for Japanese market)



Note: Please contact our sales representative for 1 Form A or 1 Form B of 24 V DC type.

ORDERING INFORMATION (TYPE NO. : Ordering part number for non Japanese market)



TYPES

[&]quot; Type No. " is ordering part number for non Japanese market. " Part No. " is ordering part number for Japanese market.

Contact	Contact		Standard type (1.8 W)			Low operating power type (1.4 W)			N)	Pac	king		
arrange-			Sealed		Dust cover		Sealed		Dust cover		Carton	Case	
ment type		voltage	Type No.	Part No.	Type No.	Part No.	Type No.	Part No.	Type No.	Part No.	Carton	Case	
1 Form A	Rubber bracket A type	_	racket A	CA1a-12V-A-5	ACA12115	CA1aF-12V-A-5	ACA42115	CA1aS-12V-A-5	ACA14115	CA1aFS-12V-A-5	ACA44115		
	Screw- mounting type		CA1a-12V-N-5	ACA12135	CA1aF-12V-N-5	ACA42135	CA1aS-12V-N-5	ACA14135	CA1aFS-12V-N-5	ACA44135			
	Direct coupling type	12 V DC	CA1a-12V-C-5	ACA12145	CA1aF-12V-C-5	ACA42145	CA1aS-12V-C-5	ACA14145	CA1aFS-12V-C-5	ACA44145			
	Rubber bracket A type	12 V DC	CA1b-12V-A-5	ACA22115	CA1bF-12V-A-5	ACA52115	CA1bS-12V-A-5	ACA24115	CA1bFS-12V-A-5	ACA54115			
1 Form B	Screw- mounting type	_	CA1b-12V-N-5	ACA22135	CA1bF-12V-N-5	ACA52135	CA1bS-12V-N-5	ACA24135	CA1bFS-12V-N-5	ACA54135	20	200	
	Direct coupling type		CA1b-12V-C-5	ACA22145	CA1bF-12V-C-5	ACA52145	CA1bS-12V-C-5	ACA24145	CA1bFS-12V-C-5	ACA54145	pcs.	pcs.	
	Screw- mounting type	- 12 V DC	CA1-DC12V-N	ACA3213	-	-	-	-	-	-			
1 Form C	Direct coupling type		CA1-DC12V-C	ACA3214	-	-	-	-	-	-			
	Screw- mounting type		CA1-DC24V-N	ACA3223	-	-	-	-	-	-			
	Direct coupling type	24 V DC	CA1-DC24V-C	ACA3224	-	-	-	-	-	-			

Note: Please use "CA**R-*-*-* or CA**SR-*-*-* with resistor inside type. (Asterisks "*" should be filled in from ORDERING INFORMATION.)

RATING

■ Coil data

1) No protective element

· ·							
Contact arrangement	Rated coil voltage	Operate voltage (at 20°C) (Initial)	Release voltage (at20°C) (Initial)	Rated operating current [±10%] (at 20°C)	Coil resistance [±10%] (at 20°C)	Rated operating power(at 20°C)	Usable voltage range
1 Form A, 1 Form B (standard type)	12 V DC	DC Max. 8 V DC	0.6 to 6 V DC	150 mA	80 Ω	1.8 W	- 10 to 16 V DC
1 Form A, 1 Form B (low operating power type)				120 mA	100 Ω	1.4 W	
1 Form C	12 V DC	Max. 8 V DC	Min. 0.6 V DC	150 mA	80 Ω	1.8 W	10 to 15 V DC
i Follii C	24 V DC	Max. 16 V DC	Min. 1.2 V DC	75 mA	320 Ω	1.0 VV	20 to 30 V DC

2) With resistor inside

Contact arrangement	Rated coil voltage	Operate voltage (at 20°C) (Initial)	Release voltage (at20°C) (Initial)	Rated operating current [±10%] (at 20°C)	Coil resistance [±10%] (at 20°C)	Rated operating power (at 20°C)	Usable voltage range
1 Form A, 1 Form B (standard type)	12 V DC	C Max. 8 V DC	0.6 to 6 V DC	160.9 mA	74.6 Ω	1.93 W	- 10 to 16 V DC
1 Form A, 1 Form B (low operating power type)				130.9 mA	91.7 Ω	1.57 W	
1 Form C	12 V DC	Max. 8 V DC	Min. 0.6 V DC	160.9 mA	74.6 Ω	1.93 W	10 to 15 V DC
I FOIIII C	24 V DC	Max. 16 V DC	Min. 1.2 V DC	80 mA	299.6 Ω	1.92 W	20 to 30 V DC

Note: Other operate voltage types are also available. Please inquire our sales representative for details.

■ Specifications

1) 12 V DC type

	Item		Specifications					
	Contact arrangement	1 Form A	1 Form B	1 Form C				
	Contact resistance (initial)	Max. 50 mΩ (typ. 3 mΩ) (By voltage drop 1 A 6 V DC)						
	Contact material	Ag alloy						
	Rated switching capacity (resistive)	20 A 12 V DC (1.4 W type) 30 A 12 V DC (1.8 W type)	20 A 12 V DC					
Contact data	Max. carrying current*1 (at coil applied voltage 14 V DC, at 80°C)	20 A continuous (1.4 W type) 30 A for 1 min (1.8 W type)						
	Min. switching load (resistive)*2	A 14 V DC (at 20°C)						
	Contact voltage drop (after electrical life)	Max. 0.3 V [at 20 A 12 V DC (1.4 W type), 30 A 12 V DC (1.8 W type) carrying]	Max. 0.3 V (at 20 A 12 V DC carrying)	Max. 0.4 V (at 20 A 12 V DC carrying)				
Insulated resista	nce (initial)	Min. 10 MΩ (at 500 V DC, Measurem	ent at same location as "Dielectric str	ength" section.)				
Dielectric	Between open contacts	500 Vrms for 1 min (Detection curren	t: 10 mA)					
strength (initial)	Between contacts and coil	500 Vrms for 1 min (Detection current: 10 mA)						
Time	Operate time (at rated voltage)	Max. 10 ms (at 20°C, without contact bounce time)	Max. 10 ms (at 20°C)	Max. 10 ms (at 20°C, without contact bounce time)				
characteristics (initial)	Release time (at rated voltage)	Max. 10 ms (at 20°C) (without diode)	Max. 10 ms (at 20°C, without contact bounce time)	Max. 10 ms (at 20°C, without contact bounce time) (without diode)				
Shock resistance	Functional	Min. 200 m/s² (Half-wave pulse of sine wave: 11 ms, detection time: 10 μs) Min. 100 m/s² (Half-wave pulse of sine wave: 11 ms, detection time: 10 μs)						
	Destructive	Min. 1,000 m/s² (Half-wave pulse of sine wave: 6 ms)						
	Functional	Rubber bracket A type: 50 to 500 Hz, Min. 100 m/s², screw-mounting type, direct coupling type JIS D1601 Type 1, Class B, stage 45, [33 Hz, 45 m/s²] (detection time: 10 µs)						
Vibration resistance	Destructive	Rubber bracket A type: 50 to 500 Hz, Min. 100 m/s², screw-mounting type, direct coupling type JIS D1601 Type 1, Class B, stage 45, [33 Hz, 45 m/s²] (Time of vibration for each direction; X, Y direction: 2 hours, Z direction: 4 hours)						
	Mechanical	Min. 10 ⁶ (at 120 times/min)		Min. 5 x 10 ⁵ (at 120 times/min)				
Expected life Electrical (at rated switching capacity)		Min. 10 ^s (operating frequency: 2 s ON, 2 s OFF) (1.4 W at 20 A) Min. 2 × 10 ⁴ (operating frequency: 2 s ON, 2 s OFF) (1.8 W type at 30 A) Min. 10 ^s (operating frequency: 2 s ON, 2 s OFF)						
Conditions Conditions for usage, transport and storage*3		Ambient temperature: -30 to +80°C, Humidity: 5 to 85% RH (Avoid icing and condensation)						
Water-proof star	ndard	Sealed: JIS D 0203 S2, Dust cover: JIS D 0203 R2						
Weight		Rubber bracket A type: approx. 23 g, Screw-mounting and direct coupling types: approx. 19 g						

©Panasonic Industry Co., Ltd. 2022

ASCTB219E 202204

Relay Users Guide".

Please inquire our sales representative if you will be using the relay in a high temperature atmosphere (110°C).

Notes: *1.Depends on connection conditions. Also, this does not guarantee repeated switching. We recommend that you confirm operation under actual conditions.

*2.This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

^{*3.}The upper operation ambient temperature limit is the maximum temperature that can satisfy the coil temperature rise value. For details, please refer to the "Automotive

2) 24 V DC type

	Item	Specifications			
	Contact arrangement	1 Form C			
	Contact resistance (initial)	Max. 50 mΩ (typ. 3 mΩ) (By voltage drop 6 V DC 1 A)			
	Contact material	Ag alloy			
Contact data	Rated switching capacity (resistive)	10 A 24 V DC			
	Max. carrying current*1	10 A continuous (at coil applied voltage 28 V DC, at 80°C)			
	Min. switching load (resistive)*2	1 A 14 V DC (at 20°C)			
	Contact voltage drop	Max. 0.4 V (after electrical life, at 24 V DC 10 A carrying)			
Insulation resista	ance (initial)	Min. 10 MΩ (at 500 V DC, Measured portion is the same as the case of dielectric strength.)			
Dielectric	Between open contacts	500 Vrms for 1 min (Detection current: 10 mA)			
strength (initial)	Between contact and coil	500 Vrms for 1 min (Detection current: 10 mA)			
Time	Operate time (at rated voltage)	Max. 10 ms (at 20°C, without contact bounce time)			
characteristics (initial)	Release time (at rated voltage)	Max. 10 ms (at 20°C, without contact bounce time) (without diode)			
Shock	Functional	Min. 100 m/s² (Half-wave pulse of sine wave: 11 ms, detection time: 10 μs)			
resistance	Destructive	Min. 1,000 m/s² (Half-wave pulse of sine wave: 6 ms)			
Vibration	Functional	JIS D1601 Type 1, Class B, stage 45, [33 Hz, 45 m/s²] (Detection time: 10 μs)			
resistance	Destructive	JIS D1601 Type 1, Class B, stage 45, [33 Hz, 45 m/s²] (Time of vibration for each direction; X, Y direction: 2 hours, Z direction: 4 hours)			
	Mechanical	Min. 5 x 10 ^s (at 120 times/min)			
Expected life	Electrical (at rated switching capacity)	Min. 10 ⁵ (operating frequency: 2 s ON, 2 s OFF)			
Conditions	Conditions for usage, transport and storage*3	Ambient temperature: -30 to +80°C, Humidity: 5 to 85% RH (Avoid icing and condensation)			
Water-proof star	ndard	JIS D 0203 S2			
Weight		approx. 31 g			

■Electrical life

1) Standard (1.8 W)

Contact arrangement	Rated coil voltage	Motor load	Halogen lamp load	
1 Form A	12 V DC	Operating frequency 3 s ON, 15 s OFF 12 V DC inlush 150 A, steady 30 A, Min. 2 x 10 ⁴	-	
1 Form B	12 V DC	Operating frequency 2 s ON, 2 s OFF 12 V DC inlush 60 A, steady 20 A, Min. 10 ⁵	Operating frequency 1 s ON, 14 s OFF 12 V DC inlush 100 A, steady 20 A, Min. 10 ⁵	
1 Form C	12 V DC	Operating frequency 2 s ON, 2 s OFF 12 V DC inlush 100 A, steady 20 A, Min. 10 ⁵	Operating frequency 1 s ON, 14 s OFF 12 V DC inlush 100 A, steady 20 A, Min. 10 ⁵	
1 FORM C	24 V DC	Operating frequency 2 s ON, 2 s OFF 24 V DC inlush 50 A, steady 10 A, Min. 10 ⁵	Operating frequency 1 s ON, 14 s OFF 24 V DC inlush 50 A, steady 6 A, Min. 10 ^s	

2) Low operating power (1.4 W)

Contact arrangement	Rated coil voltage	Motor load	Halogen lamp load	
1 Form A	12 V DC	Operating frequency 2 s ON, 2 s OFF 12 V DC inlush 120 A, steady 20 A, Min. 10 ⁵	Operating frequency 1 s ON, 14 s OFF 12 V DC inlush 100 A, steady 20 A, Min. 10 ^s	
1 Form B	12 V DC	Operating frequency 2 s ON, 2 s OFF 12 V DC inlush 60 A, steady 20 A, Min. 10 ⁵	Operating frequency 1 s ON, 14 s OFF 12 V DC inlush 100 A, steady 20 A, Min. 10 ^s	

Notes: *1. Depends on connection conditions. Also, this does not guarantee repeated switching. We recommend that you confirm operation under actual conditions.

*2. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual

^{*3.}The upper operation ambient temperature limit is the maximum temperature that can satisfy the coil temperature rise value. For details, please refer to the "Automotive Relay Users Guide".

Please inquire our sales representative if you will be using the relay in a high temperature atmosphere (110°C).

REFERENCE DATA


1.Coil temperature rise


Samples: CA1aS-12V-N-5, 5 pcs. Measured portion: Inside the coil Carrying current: 20 A Ambient temperature: Room temperature, 80°C


2. Ambient temperature and usable voltage range

3. Ambient temperature characteristics (Cold start)

Samples: CA1bS-12V-N-5









4. Distribution of operate and release voltage 5. Distribution of operate and release time

Sample: CA1a-12V-N-5, 10 pcs. Quantity: 50 pcs.







6. Electrical life test (Motor load)

Sample: CA1a-12V-C, 3 pcs. Load: Inrush current: 63 A, steady current: 23 A Blower fan motor actual load (motor free) Operating frequency: ON 2 s, OFF 2 s Ambient temperature: Room temperature


Change of operate and release voltage



Change of contact resistance



Load current waveform Load: Inrush current: 63 A, steady current: 23 A,



DIMENSIONS

CAD The CAD data of the products with a "CAD" mark can be downloaded from our Website.


Unit: mm

■1 Form A / 1 Form B Rubber bracket A type


CAD




External dimensions




21.5








Schematic (BOTTOM VIEW)






Schematic


■1 Form A / 1 Form B Screw-mounting type


CAD




External dimensions










Tolerance Max. 1mm : ±0.1 1 to 20 mm : ±0.3 Min. 20 mm : ±0.5

■1 Form A / 1 Form B Direct coupling type


CAD



External dimensions




21.5



Tolerance Max. 1mm : ±0.1 1 to 20 mm : ±0.3 Min. 20 mm : ±0.5

Schematic (BOTTOM VIEW)





Including resistor (1 Form A t)


■1 Form C Screw-mounting type


CAD

External dimensions










Tolerance Max. 1mm : ±0.1 1 to 20 mm : ±0.2 Min. 20 mm : ±0.5


■1 Form C Direct coupling type


CAD




External dimensions







Schematic



Tolerance Max. 1mm : ±0.1 1 to 20 mm : ±0.2 Min. 20 mm : ±0.5

GUIDELINES FOR USAGE

■For general cautions for use, please refer to the "Automotive Relay Users Guide".

Please refer to "the latest product specifications" when designing your product.

•Requests to customers:

https://industrial.panasonic.com/ac/e/salespolicies/

