

## Micrometer

With cylindrical and spherical measuring faces

Mitutoyo

### Application:

For measuring e.g. curved surfaces and wall thicknesses of pipes, bearings, rings, etc.

### Version:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

### Delivery:

Includes box, setting standard (from 25 mm), adjustment wrench



|   |                                      |
|---|--------------------------------------|
| <b>Art. no.</b>                         | <b>32016 626</b>                     |
| <b>Min./max. length measuring range</b> | 50-75 mm                             |
| <b>Vernier scale</b>                    | 0.01 mm                              |
| <b>Measuring spindle increments</b>     | 0.5 mm                               |
| <b>Spindle clamping</b>                 | Yes                                  |
| <b>Error limit</b>                      | 3 µm                                 |
| <b>Display</b>                          | Nonius                               |
| <b>Calibration Group</b>                | D                                    |
| <b>Type</b>                             | F – with spherical spindle and anvil |
| <b>Min./max. measurement force</b>      | 5-10 N                               |

### EAN-Code

4946368010748