
















723 2238
723 2275

Amp	Volt	Hz	IP Ident. colour + h	Part No.	Couplers	2 P +  IEC/EN 60 309	  9	EAN No. 4015609...																														
16	230	50/60	 IP44	6 316 306	mondo angled coupler, RAL 7035 light grey   		10 138	016310 016303 016327																														
	110	50/60	4 316 304																																			
	400	50/60	9 316 309																																			
<table border="1"> <thead> <tr> <th>Ampère</th> <th>d</th> <th>e</th> <th>f</th> <th>p</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>95</td> <td>50,3</td> <td>80</td> <td>8/13</td> </tr> </tbody> </table>									Ampère	d	e	f	p	16 A	95	50,3	80	8/13																				
Ampère	d	e	f	p																																		
16 A	95	50,3	80	8/13																																		
16	230	50/60	 IP44	6 317 306	angled coupler, with Schuko socket outlet on reverse side   		10 152	016341																														
			4																																			
			9																																			
<table border="1"> <thead> <tr> <th>Ampère</th> <th>a</th> <th>d</th> <th>e</th> <th>f</th> <th>Øp</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>54</td> <td>87</td> <td>49,5</td> <td>140</td> <td>7/13</td> </tr> </tbody> </table>									Ampère	a	d	e	f	Øp	16 A	54	87	49,5	140	7/13																		
Ampère	a	d	e	f	Øp																																	
16 A	54	87	49,5	140	7/13																																	
16	230	50/60	 IP67	6 319 306	gland entry   		10	016372 016365 016389																														
			4 319 304																																			
			9 319 309																																			
	32	230	50/60	6 339 306						10	017294 017287 017300																											
				4 339 304																																		
				9 339 309																																		
	63	230	50/60	6 369 306						5	017874 017867 017881																											
				4 369 304																																		
				9 369 309																																		
	125	230	50/60	6 379 306						2	018055 018048 160730																											
				4 379 304																																		
				9 379 309																																		
<table border="1"> <thead> <tr> <th>Ampère</th> <th>d</th> <th>f</th> <th>m</th> <th>u</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>136</td> <td>78</td> <td>121</td> <td>72</td> <td>13,5</td> </tr> <tr> <td>32 A</td> <td>170</td> <td>96</td> <td>149</td> <td>96</td> <td>21</td> </tr> <tr> <td>63 A</td> <td>255</td> <td>117</td> <td>206</td> <td>110</td> <td>36</td> </tr> <tr> <td>125 A</td> <td>332</td> <td>130</td> <td>275</td> <td>130</td> <td>48</td> </tr> </tbody> </table>									Ampère	d	f	m	u	Pg	16 A	136	78	121	72	13,5	32 A	170	96	149	96	21	63 A	255	117	206	110	36	125 A	332	130	275	130	48
Ampère	d	f	m	u	Pg																																	
16 A	136	78	121	72	13,5																																	
32 A	170	96	149	96	21																																	
63 A	255	117	206	110	36																																	
125 A	332	130	275	130	48																																	
with Multi Contact																																						