

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
 - **Trade name: UHU plus endfest 300 (Binder)**
 - **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
 - **Application of the substance / the mixture** Adhesives
 - **1.3 Details of the supplier of the safety data sheet**
 - **Manufacturer/Supplier:**
UHU GmbH & Co.KG
Herrmannstraße 7
D-77815 Bühl (Baden)
Tel.: 0049-(0)7223-284-0
email: sds@uhu.boltongroup.com
Fax: 0049-(0)7223-284-245
 - **Further information obtainable from:** UHU QESH
 - **1.4 Emergency telephone number:**
Tel.: + 49 (0) 30/19240 (Notruf)
Tel.: + 49 (0) 72 23/28 40
- England and Wales (NHS Direct) 111
Schottland (NHS 24) 111

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS09 environment

Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.



GHS07

Skin Irrit. 2 H315 Causes skin irritation.
Eye Irrit. 2 H319 Causes serious eye irritation.
Skin Sens. 1 H317 May cause an allergic skin reaction.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 1)

Hazard pictograms


GHS07 GHS09

Signal word Warning

Hazard-determining components of labelling:

 reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700)

 reaction product: bisphenol-F-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700)

Hazard statements

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H317 May cause an allergic skin reaction.

H411 Toxic to aquatic life with long lasting effects.

Precautionary statements

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

P261 Avoid breathing vapours.

P280 Wear protective gloves.

P302+P352 IF ON SKIN: Wash with plenty of soap and water.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P501 Dispose of contents/container in accordance with national regulations.

Additional information:

Contains epoxy constituents. May produce an allergic reaction.

2.3 Other hazards
Results of PBT and vPvB assessment
PBT: Not applicable.

vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

3.2 Mixtures
Description:

Mixture of substances listed below with nonhazardous additions.

Adhesive

Dangerous components:


CAS: 25068-38-6

NLP: 500-033-5

Reg.nr.: 01-2119456619-26-XXXX

 reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight \leq 700)

50-100%



(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 2)

CAS: 9003-36-5

Reg.nr.: 01-2119454392-40-xxxx

 reaction product: bisphenol-F-(epichlorhydrin)
 epoxy resin (number average molecular weight \leq
 700)

2.5-10%

 ⚠ Aquatic Chronic 2, H411; ⚠ Skin Irrit. 2, H315;
 Skin Sens. 1, H317

- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:**
 Supply fresh air and to be sure call for a doctor.
 In case of unconsciousness place patient stably in side position for transportation.
 Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:**
 Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**
 Rinse out mouth and then drink plenty of water.
 Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
 No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
 No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
 Water spray
 Carbon dioxide
 Foam
 Fire-extinguishing powder
 Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture**
 Formation of toxic gases is possible during heating or in case of fire.
 In case of fire, the following can be released:
 Carbon monoxide (CO)
- **5.3 Advice for firefighters**
- **Protective equipment:** Do not inhale explosion gases or combustion gases.

EU-EN

(Contd. on page 4)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 3)

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Ensure adequate ventilation
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Send for recovery or disposal in suitable receptacles.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Store in cool, dry place in tightly closed receptacles.
Prevent formation of aerosols.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store only in the original receptacle.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**
Store receptacle in a well ventilated area.
Keep container tightly sealed.
- **Storage class:** 10
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures are to be adhered to when handling chemicals.
Keep away from foodstuffs, beverages and feed.

(Contd. on page 5)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 4)

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes and skin.

· **Respiratory protection:**

Not necessary if room is well-ventilated.

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Recommended filter device for short term use:** Combination filter A-P1

· **Protection of hands:**

Rubber gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation



Protective gloves

· **Material of gloves**

Hand protection Material : butyl-rubber (e.g. Butoject 898: material thickness 0,7 mm)

Break through time : > 8 h

Material : Ethyl Vinyl Alcohol Laminate (EVAL)

Break through time : > 8 h

glove material for short-term use / splash: (10 min <BTT <480 min): nitrile rubber, neoprene rubber

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it. Gloves should be discarded and replaced if there is any indication of degradation or chemical breakthrough. Take note of the information given by the producer concerning permeability and break through times, and of special workplace conditions (mechanical strain, duration of contact). The suitability for a specific workplace should be discussed with the producers of the protective gloves.

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 5)

· Eye protection:



Safety glasses

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

Form:	Fluid
Colour:	Colourless
· Odour:	Weak, characteristic
· Odour threshold:	Not determined.

· pH-value at 20 °C: 6

· Change in condition

Melting point/freezing point:	Undetermined.
Initial boiling point and boiling range:	Undetermined.

· Flash point: >150 °C

· Flammability (solid, gas): Not applicable.

· Decomposition temperature: Not determined.

· Auto-ignition temperature: Product is not selfigniting.

· Explosive properties: Product does not present an explosion hazard.

· Explosion limits:

Lower:	Not determined.
Upper:	Not determined.

· Vapour pressure: Not determined.

 · Density at 20 °C: 1.15 g/cm³

· Relative density: Not determined.

· Vapour density: Not determined.

· Evaporation rate: Not determined.

· Solubility in / Miscibility with

water: Not miscible or difficult to mix.

· Partition coefficient: n-octanol/water: Not determined.

· Viscosity:

Dynamic at 20 °C:	40000 mPas
Kinematic:	Not determined.

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 6)

· Solvent content: VOC (EC)	0.00 %
· Solids content:	91.0 %
· 9.2 Other information	All relevant physical data were determined for the mixture. All non determined data are not measurably or not relevant for the characterization of the mixture.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions**
Exothermic polymerisation.
Reacts with amines.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation**
Causes skin irritation.
- **Serious eye damage/irritation**
Causes serious eye irritation.
- **Respiratory or skin sensitisation**
May cause an allergic skin reaction.
- **Acute effects (acute toxicity, irritation and corrosivity)** Not applicable.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.

(Contd. on page 8)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 7)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Toxic for fish
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Danger to drinking water if even small quantities leak into the ground.
Also poisonous for fish and plankton in water bodies.
Toxic for aquatic organisms
Do not allow product to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
Disposal must be made according to official regulations.

· **European waste catalogue**

08 04 09*	waste adhesives and sealants containing organic solvents or other hazardous substances
-----------	--

- **Uncleaned packaging:**
- **Recommendation:**
Packagings that may not be cleansed are to be disposed of in the same manner as the product.

SECTION 14: Transport information

- | | |
|---|---|
| <ul style="list-style-type: none"> · 14.1 UN-Number · ADR, IMDG, IATA | UN3082 |
| <ul style="list-style-type: none"> · 14.2 UN proper shipping name · ADR | 3082 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight ≤ 700), reaction product: bisphenol-F-(epichlorhydrin) epoxy resin (number average molecular weight ≤ 700))
3082 UMWELTGEFÄHRDENDER STOFF, FLÜSSIG, N.A.G. (Reaktionsprodukt: Bisphenol-A- |

(Contd. on page 9)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 8)

<ul style="list-style-type: none"> · IMDG · IATA 	Epichlorhydrinharze mit durchschnittlichem Molekulargewicht ≤ 700 , Bisphenol-F-Epichlorhydrinharze MG < 700 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight ≤ 700), reaction product: bisphenol-F-(epichlorhydrin) epoxy resin (number average molecular weight ≤ 700)), MARINE POLLUTANT ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (reaction product: bisphenol-A-(epichlorhydrin) epoxy resin (number average molecular weight ≤ 700), reaction product: bisphenol-F-(epichlorhydrin) epoxy resin (number average molecular weight ≤ 700))
--	---

<ul style="list-style-type: none"> · 14.3 Transport hazard class(es) · ADR, IMDG, IATA 	9 Miscellaneous dangerous substances and articles. 9
--	---



<ul style="list-style-type: none"> · Class · Label 	9 Miscellaneous dangerous substances and articles. 9
--	---

<ul style="list-style-type: none"> · 14.4 Packing group · ADR, IMDG, IATA 	III
---	-----

<ul style="list-style-type: none"> · 14.5 Environmental hazards: · Marine pollutant: · Special marking (ADR): · Special marking (IATA): 	Yes Symbol (fish and tree) Symbol (fish and tree) Symbol (fish and tree)
---	---

<ul style="list-style-type: none"> · 14.6 Special precautions for user · Danger code (Kemler): · EMS Number: · Stowage Category 	Warning: Miscellaneous dangerous substances and articles. 90 F-A,S-F A
---	---

<ul style="list-style-type: none"> · 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code 	Not applicable.
--	-----------------

(Contd. on page 10)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 9)

· Transport/Additional information:
· ADR
· Limited quantities (LQ)

5L

· Excepted quantities (EQ)

Code: E1

Maximum net quantity per inner packaging: 30 ml

Maximum net quantity per outer packaging: 1000 ml

· Transport category

3

· Tunnel restriction code

-

· IMDG
· Limited quantities (LQ)

5L

· Excepted quantities (EQ)

Code: E1

Maximum net quantity per inner packaging: 30 ml

Maximum net quantity per outer packaging: 1000 ml

· UN "Model Regulation":

 UN 3082 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (REACTION PRODUCT: BISPHENOL-A-(EPICHLORHYDRIN) EPOXY RESIN (NUMBER AVERAGE MOLECULAR WEIGHT \leq 700), REACTION PRODUCT: BISPHENOL-F-(EPICHLORHYDRIN) EPOXY RESIN (NUMBER AVERAGE MOLECULAR WEIGHT \leq 700)), 9, III

SECTION 15: Regulatory information

· 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
· Directive 2012/18/EU
· Named dangerous substances - ANNEX I None of the ingredients is listed.

· Seveso category E2 Hazardous to the Aquatic Environment

· Qualifying quantity (tonnes) for the application of lower-tier requirements 200 t

· Qualifying quantity (tonnes) for the application of upper-tier requirements 500 t

· REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H315 Causes skin irritation.

(Contd. on page 11)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 26

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Binder)

(Contd. of page 10)

H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H411 Toxic to aquatic life with long lasting effects.

· **Department issuing SDS:** UHU QESH

· **Contact:** Dr. C. Hanf

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

Skin Sens. 1: Skin sensitisation – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

· * **Data compared to the previous version altered.**

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier**Trade name: UHU plus endfest 300 (Härter)****1.2 Relevant identified uses of the substance or mixture and uses advised against**

No further relevant information available.

Application of the substance / the mixture Adhesives**1.3 Details of the supplier of the safety data sheet****Manufacturer/Supplier:**

UHU GmbH & Co.KG

Herrmannstraße 7

D-77815 Bühl (Baden)

Tel.: 0049-(0)7223-284-0

email: sds@uhu.boltongroup.com

Fax: 0049-(0)7223-284-245

Further information obtainable from: UHU QESH**1.4 Emergency telephone number:**

Tel.: + 49 (0) 30/19240 (Notruf)

Tel.: + 49 (0) 72 23/28 40

England and Wales (NHS Direct) 111

Schottland (NHS 24) 111

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture**Classification according to Regulation (EC) No 1272/2008**

GHS05 corrosion

Skin Corr. 1B H314 Causes severe skin burns and eye damage.

Eye Dam. 1 H318 Causes serious eye damage.



GHS07

Skin Sens. 1 H317 May cause an allergic skin reaction.

2.2 Label elements**Labelling according to Regulation (EC) No 1272/2008**

The product is classified and labelled according to the CLP regulation.

Hazard pictograms

GHS05 GHS07

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Härter)

(Contd. of page 1)

- **Signal word** Danger
- **Hazard-determining components of labelling:**
N'-(3-aminopropyl)-N,N-dimethylpropane-1,3-diamine amine, polyethylenepoly-, triethylenetetramine fraction
- **Hazard statements**
H314 Causes severe skin burns and eye damage.
H317 May cause an allergic skin reaction.
- **Precautionary statements**
P101 If medical advice is needed, have product container or label at hand.
P102 Keep out of reach of children.
P260 Do not breathe vapours.
P280 Wear protective gloves / eye protection.
P301+P330+P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P302+P352 IF ON SKIN: Wash with plenty of soap and water.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P501 Dispose of contents/container in accordance with national regulations.
- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**
- **Description:**
Mixture of substances listed below with nonhazardous additions.
Adhesive

- **Dangerous components:**

CAS: 10563-29-8 EINECS: 234-148-4	N'-(3-aminopropyl)-N,N-dimethylpropane-1,3-diamine ⚠ Skin Corr. 1B, H314; ⚠ Acute Tox. 4, H302; Skin Sens. 1, H317	2.5-10%
CAS: 90640-67-8 EINECS: 292-588-2 Reg.nr.: 01-2119487919-13	amine, polyethylenepoly-, triethylenetetramine fraction ⚠ Skin Corr. 1B, H314; Eye Dam. 1, H318; ⚠ Acute Tox. 4, H302; Acute Tox. 4, H312; Skin Sens. 1, H317; Aquatic Chronic 3, H412	2.5-10%

- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:**
Supply fresh air and to be sure call for a doctor.

(Contd. on page 3)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Härter)

(Contd. of page 2)

- In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:**
Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
Water spray
Carbon dioxide
Foam
Fire-extinguishing powder
Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture**
Formation of toxic gases is possible during heating or in case of fire.
In case of fire, the following can be released:
Nitrogen oxides (NO_x)
Carbon monoxide (CO)
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters**
- **Protective equipment:**
Do not inhale explosion gases or combustion gases.
Mouth respiratory protective device.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Mount respiratory protective device.
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Send for recovery or disposal in suitable receptacles.
Use neutralising agent.
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.

(Contd. on page 4)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Härter)

(Contd. of page 3)

See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Ensure good ventilation/exhaustion at the workplace.
Store in cool, dry place in tightly closed receptacles.
Prevent formation of aerosols.

· **Information about fire - and explosion protection:** Keep respiratory protective device available.

7.2 Conditions for safe storage, including any incompatibilities**Storage:**

· **Requirements to be met by storerooms and receptacles:** Store only in the original receptacle.

· **Information about storage in one common storage facility:** Not required.

Further information about storage conditions:

Store receptacle in a well ventilated area.
Keep container tightly sealed.

· **Storage class:** 8 A

· **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

· **Additional information about design of technical facilities:** No further data; see item 7.

8.1 Control parameters**Ingredients with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· **Additional information:** The lists valid during the making were used as basis.

8.2 Exposure controls**Personal protective equipment:****General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
Avoid contact with the eyes and skin.

Respiratory protection:

Not necessary if room is well-ventilated.

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Recommended filter device for short term use:** Combination filter A-P1

(Contd. on page 5)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Härter)

(Contd. of page 4)

· **Protection of hands:**

Rubber gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation



Protective gloves

· **Material of gloves**

Hand protection Material : butyl-rubber (e.g. Butoject 898: material thickness 0,7 mm)

Break through time : > 8 h

Material : Ethyl Vinyl Alcohol Laminate (EVAL)

Break through time : > 8 h

glove material for short-term use / splash: (10 min <BTT <480 min): nitrile rubber, neoprene rubber

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it. Gloves should be discarded and replaced if there is any indication of degradation or chemical breakthrough. Take note of the information given by the producer concerning permeability and break through times, and of special workplace conditions (mechanical strain, duration of contact). The suitability for a specific workplace should be discussed with the producers of the protective gloves.

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Safety glasses

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form:

Fluid

Colour:

Yellow

· **Odour:**

Amine-like

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Härter)

(Contd. of page 5)

· Odour threshold:	Not determined.
· pH-value at 20 °C:	12 (1:1 in H ₂ O)
· Change in condition Melting point/freezing point: Initial boiling point and boiling range:	Undetermined. ~278 °C
· Flash point:	>100 °C
· Flammability (solid, gas):	Not applicable.
· Ignition temperature:	335 °C
· Decomposition temperature:	Not determined.
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product does not present an explosion hazard.
· Explosion limits: Lower: Upper:	Not determined. Not determined.
· Vapour pressure:	Not determined.
· Density at 20 °C: · Relative density · Vapour density · Evaporation rate	0.95 g/cm ³ Not determined. Not determined. Not determined.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity: Dynamic at 20 °C: Kinematic:	32500 mPas Not determined.
· Solvent content: VOC (EC)	0.00 %
· Solids content: · 9.2 Other information	84.2 % All relevant physical data were determined for the mixture. All non determined data are not measurably or not relevant for the characterization of the mixture.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.

(Contd. on page 7)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Härter)

(Contd. of page 6)

- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**

90640-67-8 amine, polyethylenepoly-,triethylenetetramine fraction

Oral	LD50	2500 mg/kg (rat)
Dermal	LD50	805 mg/kg (rabbit)

- **Primary irritant effect:**
- **Skin corrosion/irritation**
Causes severe skin burns and eye damage.
- **Serious eye damage/irritation**
Causes serious eye damage.
- **Respiratory or skin sensitisation**
May cause an allergic skin reaction.
- **Acute effects (acute toxicity, irritation and corrosivity)** Not applicable.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Must not reach sewage water or drainage ditch undiluted or unneutralised.
Danger to drinking water if even small quantities leak into the ground.
Do not allow product to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

(Contd. on page 8)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Härter)

(Contd. of page 7)

- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**

- **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

Disposal must be made according to official regulations.

- **European waste catalogue**

08 04 09*	waste adhesives and sealants containing organic solvents or other hazardous substances
-----------	--

- **Uncleaned packaging:**

- **Recommendation:**

Packagings that may not be cleansed are to be disposed of in the same manner as the product.

SECTION 14: Transport information

- **14.1 UN-Number**

- **ADR, IMDG, IATA**

UN2735

- **14.2 UN proper shipping name**

- **ADR**

2735 POLYAMINES, LIQUID, CORROSIVE, N.O.S. (N'-(3-aminopropyl)-N,N-dimethylpropane-1,3-diamine, amine, polyethylenepoly-,triethylenetetramine fraction)

- **IMDG, IATA**

POLYAMINES, LIQUID, CORROSIVE, N.O.S. (N'-(3-aminopropyl)-N,N-dimethylpropane-1,3-diamine, amine, polyethylenepoly-,triethylenetetramine fraction)

- **14.3 Transport hazard class(es)**

- **ADR, IMDG, IATA**



- **Class**

8 Corrosive substances.

- **Label**

8

- **14.4 Packing group**

- **ADR, IMDG, IATA**

III

(Contd. on page 9)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Härter)

(Contd. of page 8)

14.5 Environmental hazards:

 · **Marine pollutant:** No

14.6 Special precautions for user

· Danger code (Kemler): · EMS Number: · Segregation groups · Stowage Category · Segregation Code	Warning: Corrosive substances. 80 F-A,S-B Alkalis A SG35 Stow "separated from" SGG1-acids
---	--

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable.

Transport/Additional information:
ADR

· Limited quantities (LQ) · Excepted quantities (EQ)	5L Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· Transport category · Tunnel restriction code	3 E

IMDG

· Limited quantities (LQ) · Excepted quantities (EQ)	5L Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
---	--

UN "Model Regulation":

UN 2735 POLYAMINES, LIQUID, CORROSIVE, N.O.S. (N'-(3-AMINOPROPYL)-N,N-DIMETHYLPROPANE-1,3-DIAMINE, AMINE, POLYETHYLENEPOLY-, TRIETHYLENETETRAMINE FRACTION), 8, III

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
Directive 2012/18/EU

 · **Named dangerous substances - ANNEX I** None of the ingredients is listed.

 · **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3

 · **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

EU-EN

(Contd. on page 10)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 05.07.2019

Version number 29

Revision: 05.07.2019

Trade name: UHU plus endfest 300 (Härter)

(Contd. of page 9)

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

- H302 Harmful if swallowed.
- H312 Harmful in contact with skin.
- H314 Causes severe skin burns and eye damage.
- H317 May cause an allergic skin reaction.
- H318 Causes serious eye damage.
- H412 Harmful to aquatic life with long lasting effects.

· Department issuing SDS: UHU QESH**· Contact: Dr. C. Hanf****· Abbreviations and acronyms:**

- ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
- IMDG: International Maritime Code for Dangerous Goods
- IATA: International Air Transport Association
- GHS: Globally Harmonised System of Classification and Labelling of Chemicals
- EINECS: European Inventory of Existing Commercial Chemical Substances
- ELINCS: European List of Notified Chemical Substances
- CAS: Chemical Abstracts Service (division of the American Chemical Society)
- VOC: Volatile Organic Compounds (USA, EU)
- LC50: Lethal concentration, 50 percent
- LD50: Lethal dose, 50 percent
- PBT: Persistent, Bioaccumulative and Toxic
- vPvB: very Persistent and very Bioaccumulative
- Acute Tox. 4: Acute toxicity – Category 4
- Skin Corr. 1B: Skin corrosion/irritation – Category 1B
- Eye Dam. 1: Serious eye damage/eye irritation – Category 1
- Skin Sens. 1: Skin sensitisation – Category 1
- Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

· * Data compared to the previous version altered.