

Front-mounted sliding door, 2-part

For HK tool shelf

Application:

The sliding doors can be used to turn two shelf bays into one cabinet with sliding doors.

Execution:

- From sheet steel, canted
- Projection depth 95 mm
- Drawers or fixed or pull-out, height-adjustable shelves can be installed behind the front-mounted sliding doors
- When requesting/ordering, please indicate the RAL colours required.

Art. no.	50548 545
Brand	HK
Manufacturer Part Number	50548545
Colour	Optional
Suitable for width	1400 mm
Surface	Powder-coated
Material	Sheet steel
Gross Weight	45.500 kg
Product Group	501



EAN

4039247697328