

Pivot plier wrench

industrial version



Execution:

- Special steel
- Rounded edges
- With suspension hole
- Extended hook and shank
- Reinforced rivet
- Surface annealed in burnished finish

Advantage:

- Longer shank for greater transferable torque
- Reinforced rivet for longer service life with greater force transmission
- Even movement with additional spring washer
- One-hand operation possible
- Excellent material strength with low-tension microstructure



Art. no.	52106 060
Brand	AMF
Manufacturer Part Number	53082
Suitable for nut type	Round nut with set pin holes DIN 1816
Suitable for min./max. nut male thread size	60-90 mm
Diameter of tenon	6 mm
Length	280 mm
Gross Weight	0.364 kg
Product Group	532

EAN

4020772053086