

Balancer with load capacity of 150.0-300.0 kg

Type 7261, cable extraction 1500 mm

AUTOSTAT

Application:

Can be used for following tools and devices, e. g.: Riveting tongs, butcher's machines etc.

Execution:

- Housing and the cable drum made of aluminium sand cast
- Cable drum double ball bearings
- Suspension can be tilted and positioned to the load
- Carrying force is infinitely variable via adjusting screw
- Load is attached via a safety hook with hook mouth protection on an encapsulated deflection roller
- Cable feed limitation is impact absorbing and adjustable
- Rope is infinitely variable in its length via a rope clamp
- If required, the cable can be replaced very easily
- Safety device: Fall arrester in line with DIN 15112 included in scope of delivery, patented over-twist safeguard of suspension spring, spring safety device, fully encapsulated special motive spring, cable drum, can be blocked with integrated locking device, push clamp for securing the cable end
- Working area: Cable extraction: 1500 mm, ropes in special lengths available on request

Advantage:

- Effortless work



Art. no.	7700 903
Brand	AUTOSTAT
Manufacturer Part Number	77000903
Min. load-carrying capacity	200 kg
Max. load-carrying capacity	225 kg
Type	7261
With automatic locking	No
Max. cable pull-out length	1500 mm
Adjustable cord length	Yes
Wire cable diameter	5 mm
Replaceable cord	Yes
Cord in-feed restriction	Absorbs impacts, adjustable
Material of cable drum	Gravity die-cast aluminium
Suspension type	Freely rotating and pivot safety hook, positionable
Load attachment	Screw Karabiner hook
Material of housing	Gravity die-cast aluminium
Housing width	290 mm
Housing thickness	348 mm
Height	2500 mm
Spring design	Riveted special mainspring in separate spring housing
With overrotation protection	Yes
Spring breakage protection	Yes
Number of springs	2 PCS
DIN	15112
Gross Weight	49.000 kg
Product Group	772

EAN

4039247618309