


## Wood twist drills for machines chrome vanadium steel

Point cut: center point and 2 shoulder cutting edges  
 Surface: black steam tempered ground pilot point  
 Shank: straight shank

Highly efficient wood drill made of abrasion-proof chrome vanadium steel. The center point guarantees precise drilling. Exact and non-splintering drilling with the shoulder cutting edges. Ideal suitable for dowel-hole drillings.

Applications: for drilling in soft wood, hard wood, plywood, hardboards and veneer wood

Right-hand cutting

|                                    |   |
|------------------------------------|---|
| Packing unit: in plastic bags of 1 |  |
|------------------------------------|---|

| Ø mm | Total length mm | Working length mm | Article no. | Price / each € |
|------|-----------------|-------------------|-------------|----------------|
| 3,0  | 61              | 46                | 208 030     |                |
| 4,0  | 73              | 52                | 208 040     |                |
| 5,0  | 86              | 60                | 208 050     |                |
| 6,0  | 91              | 66                | 208 060     |                |
| 7,0  | 107             | 72                | 208 070     |                |
| 8,0  | 116             | 80                | 208 080     |                |
| 9,0  | 124             | 84                | 208 090     |                |
| 10,0 | 132             | 90                | 208 100     |                |
| 11,0 | 132             | 100               | 208 110     |                |
| 12,0 | 150             | 102               | 208 120     |                |
| 13,0 | 152             | 112               | 208 130     |                |
| 14,0 | 159             | 112               | 208 140     |                |
| 15,0 | 167             | 112               | 208 150     |                |
| 16,0 | 168             | 112               | 208 160     |                |
| 18,0 | 184             | 130               | 208 180     |                |
| 20,0 | 200             | 130               | 208 200     |                |
| 22,0 | 200             | 130               | 208 220     |                |
| 24,0 | 200             | 130               | 208 240     |                |
| 26,0 | 200             | 130               | 208 260     |                |
| 28,0 | 200             | 130               | 208 280     |                |
| 30,0 | 200             | 130               | 208 300     |                |

