



## Technical details

Approvals:	CE;cULus Listed;TÜV;KOSHA;CCC
Application options:	Safety gate monitor;Instantaneous E-STOP monitoring;Limit switch;Light beam device mon. Type 4;Light beam device mon. Type 2 w/o t/p;Light beam device mon. Type 2 with t/p
Operating modes:	Single-channel;Automatic reset;Dual-channel;Manual reset;Detection of shorts across contacts;Start-up testing;Monitored manual reset;without detection of shorts across contacts;Self test
Product standard:	EN 60947-5-1
Standards:	EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1
Supply voltage (V):	48,0 - 240,0
Supply voltage type:	AC/DC
Terminal style:	Plug-in
Terminal type:	Screw terminal
Number of instantaneous safety contacts:	3
Number of auxiliary contacts:	1
Number of semiconductor outputs:	1
Stop category:	0
Max. current at DC13 I (6 cycles/min):	4.0 A
Max. current at AC15:	3.0 A
Width dimension:	22.5 mm
Height dimension:	98.0 mm
Depth dimension:	120.0 mm

Gross weight:	220 g
Net weight:	210 g
Ambient temperature:	-10 - 55 °C