

FLH-T

FAN HEATER WITH INTEGRATED THERMOSTAT 250–1000 W

Pfannenberger heater line with integrated thermostat. This line has been specifically developed for demanding environments, especially wind turbines and for use in the telecommunications sector.

- all tests were performed according to European Norms, EN 60068-2-6 / 60068-2-27 / 60068-2-29 Railway applications - Rolling stock equipment - Shock and vibration tests and therefore are unique to the industry
- can be used under extreme conditions (- 40 °C...+ 70 °C)
- fan design with ball bearing: guaranteed long service life
- voltage range: 230 V / 115 V / 50/60 Hz



PRODUCT		FLH-T 250	FLH-T 400	FLH-T 600	FLH-T 800	FLH-T 1000	
ARTICLE NO.	230 V	17025310007	17040310007	17060310007	17080310007	17099310007	Unit
ARTICLE NO.	115 V	17025315007	17040315007	17060315007	17080315007	17099315007	

DATA							
Heating performance (Ta = +20 °C)		250	400	600	800	1000	W
Rated voltage ±10 %	AC 50 60 Hz						
	230						V
Functional range	104–127 V or 207–258 V AC 50 60 Hz						
Max. starting current		0.7	2.6	3.4	4.3	5.2	A
Bearing type	ball bearing						
Service life L ₁₀ (+ 25 °C)	52500						h
Switching temperature difference	< 7						K
Switching point tolerance	± 4						
Temperature setting range	-20 ... +40						°C
Operating temperature	-40 ... +70						
Volumetric air flow	50 Hz	160					m ³ /h
	60 Hz	180					
System of protection for intended purpose of use	IP 20						
Protection class	II (double insulation)						
Device construction	plastic UL 94V-0, black						
Type of mounting	4 x M5 screws (not included)						
Type of connection	2-pole terminal strip						
Weight		1.0	1.1	1.2	1.4		kg

ACCESSORIES	ARTICLE NUMBER
Hygrostat	17207000000
Internal enclosure fan	18110000000

For additional models, options and voltages visit www.pfannenberger.com or contact us directly.



Dimensions

mm	FLH-T
X	150
X1	138
X2	6
X3	5.4
Y	100
Z	164
Z1	100
Z2	13.3
Z3	5

