TGS 2600 - for the detection of Air Contaminants

Features:

* Low power consumption

FIGARO

- * High sensitivity to gaseous air contaminants
- * Long life and low cost
- * Uses simple electrical circuit
- * Small size

Applications:

- * Air cleaners
- * Ventilation control
- * Air quality monitors

The sensing element is comprised of a metal oxide semiconductor layer formed on an alumina substrate of a sensing chip together with an integrated heater. In the presence of a detectable gas, the sensor's conductivity increases depending on the gas concentration in the air. A simple electrical circuit can convert the change in conductivity to an output signal which corresponds to the gas concentration.


The **TGS 2600** has high sensitivity to low concentrations of gaseous air contaminants such as hydrogen and carbon monoxide which exist in cigarette smoke. The sensor can detect hydrogen at a level of several ppm. Figaro also offers a microprocessor (FIC02667) which contains special software for handling the sensor's signal for appliance control applications.

Due to miniaturization of the sensing chip, TGS 2600 requires a heater current of only 42mA and the device is housed in a standard TO-5 package.


The figure below represents typical sensitivity characteristics, all data having been gathered at standard test conditions (see reverse side of this sheet). The Y-axis is indicated as sensor resistance ratio (Rs/Ro) which is defined as follows:

Rs = Sensor resistance in displayed gases at various concentrations

Ro = Sensor resistance in fresh air




Sensitivity Characteristics:



The figure below represents typical temperature and humidity dependency characteristics. Again, the Y-axis is indicated as sensor resistance ratio (Rs/Ro), defined as follows:

Rs = Sensor resistance in fresh air at various temperatures/humidities Ro = Sensor resistance in fresh air at 20°C and 65% R.H.

Temperature/Humidity Dependency:




IMPORTANT NOTE: OPERATING CONDITIONS IN WHICH FIGARO SENSORS ARE USED WILL VARY WITH EACH CUSTOMER'S SPECIFIC APPLICATIONS. FIGARO STRONGLY RECOMMENDS CONSULTING OUR TECHNICAL STAFF BEFORE DEPLOYING FIGARO SENSORS IN YOUR APPLICATION AND, IN PARTICULAR, WHEN CUSTOMER'S TARGET GASES ARE NOT LISTED HEREIN. FIGARO CANNOT ASSUME ANY RESPONSIBILITY FOR ANY USE OF ITS SENSORS IN A PRODUCT OR APPLICATION FOR WHICH SENSOR HAS NOT BEEN SPECIFICALLY TESTED BY FIGARO.

Basic Measuring Circuit:

The sensor requires two voltage inputs: heater voltage (VH) and circuit voltage (Vc). The heater voltage (VH) is applied to the integrated heater in order to maintain the sensing element at a specific temperature which is optimal for sensing. Circuit voltage (Vc) is applied to allow measurement of voltage (Vout) across a load resistor (RL) which is connected in series with the sensor.

DC voltage is required for the circuit


voltage since the sensor has a polarity. A common power supply circuit can be used for both Vc and V_H to fulfill the sensor's electrical requirements. The value of the load resistor (R_L) should be chosen to optimize the alarm threshold value, keeping power consumption (Ps) of the semiconductor below a limit of 15mW. Power consumption (Ps) will be highest when the value of Rs is equal to R_L on exposure to gas.



Structure and Dimensions:

Specifications:

Model number			TGS 2600-B00	
Sensing element type		D1		
Standard package			TO-5 metal can	
Target gases			Air contaminants	
Typical detection range			1 ~ 30 ppm of H2	
Standard circuit conditions	Heater voltage	Vн	5.0±0.2V DC/AC	
	Circuit voltage	Vc	5.0±0.2V DC	Ps ≤ 15mW
	Load resistance	R∟	Variable	0.45k Ω min.
Electrical characteristics under standard test conditions	Heater resistance	Rн	approx. 83Ω at room temp. (typical)	
	Heater current	Ін	42±4mA	
	Heater power consumption	Рн	210mW	VH=5.0V DC
	Sensor resistance	Rs	10k~90k Ω in air	
	Sensitivity (change ratio of Rs)		0.3~0.6	<u>Rs (10ppm of H2)</u> Rs (air)
Standard test conditions	Test gas conditions		normal air at 20±2°C, 65±5%RH	
	Circuit conditions		Vc = 5.0±0.01V DC VH = 5.0±0.05V DC	
	Conditioning period before test		7 days	




Sensor resistance (Rs) is calculated with a measured value of Vout by using the following formula:

$$Ps = \frac{(Vc - Vout)^2}{Rs}$$

$$Rs = \frac{V_{C} \times R_{L}}{V_{O} ut} - R_{L}$$

For information on warranty, please refer to Standard Terms and Conditions of Sale of Figaro USA Inc. All sensor characteristics shown in this brochure represent typical characteristics. Actual characteristics vary from sensor to sensor. The only characteristics warranted are those in the Specification table above.



121 S. Wilke Rd. Suite 300 Arlington Heights, IL 60005 Phone: (847)-832-1701 Fax: (847)-832-1705 e-mail: figarousa@figarosensor.com

REV: 01/05