

TB Davies EN131 Pro Quadra Platform Step Ladder



[Representative image of product]

Features

- Featuring tough spun-rung 'Duraclimb' technology for intensive use
- Comfortable 75 degree safe-climbing angle
- Large 85mm deep steps for fatigue-free standing
- Solid die-cast aluminium safety platform
- High strength nylon components reduce wear and tear
- Durable die-cast hinges
- Spacious storage tray for material and tools

Product Dimensions

SKU	Treads ²	Approx. Working Height ¹ (mm)	Platform Height (mm)	Open Height (mm)	Closed Height (mm)	Width (mm)	Open Depth (mm)	Nett Weight (kg)
1211-003	3	2300	700	1300	1400	440	650	4.5
1211-004	4	2500	900	1500	1600	470	810	5.2
1211-005	5	2700	1100	1700	1900	500	970	6.8
1211-006	6	3000	1400	2000	2100	530	1130	7.5
1211-007	7	3200	1600	2200	2400	560	1330	8.3
1211-008	8	3400	1800	2400	2600	590	1480	9.5
1211-009	9	3700	2100	2700	2900	620	1640	11.2
1211-010	10	3900	2300	2900	3100	650	1840	12.0
1211-012	12	4400	2800	3400	3600	710	2150	14.2

¹ Working height is calculated as 1,600mm plus platform height or last climbing tread, whichever is appropriate. Ladders set at an angle of 75° degrees.

² Treads includes top platform step/top cap tool tray tread

Specifications

- Warranty: 5-year
- Standard: EN131 Professional
- Material: Aluminium
- Commodity Code: 76169990
- Country of Origin: IT
- Recommended Usage: Intensive

Common Dimensions

- Tread Depth: 85mm
- Distance Between Treads: 250mm
- Storage Depth: 140mm
- Top Platform Tread (LxW): 265 x 265mm
- Handrail Height: 600mm

Availability & Delivery

Stock item. Delivery next day.
(See exceptions, if applicable, overleaf)

TB Davies EN131 Pro Quadra Platform Step Ladder

Product Description

The Quadra platform step ladder is designed for intensive use and features a large cast aluminium safety platform set at a comfortable 75-degree angle. The large 85mm deep treads are secured using 'Duraclimb' spun-rung technology to provide the strongest possible mechanical connection for intensive use.

Shipping Dimensions

SKU	Barcode	Shipping Length (mm)	Shipping Width (mm)	Shipping Depth (mm)	Shipping Volume (m ³)	Gross Weight (kg)
1211-003	8028406002406	1400	440	115	0.071	4.5
1211-004	8028406002413	1600	470	115	0.086	5.2
1211-005	8028406002420	1900	500	115	0.109	6.8
1211-006	8028406002437	2100	530	115	0.128	7.5
1211-007	8028406002444	2400	560	115	0.155	8.3
1211-008	8028406002451	2600	590	115	0.176	9.5
1211-009	8028406002468	2900	620	140	0.252	11.2
1211-010	8028406002475	3100	650	140	0.282	12.0
1211-012	8028406002499	3600	710	140	0.358	14.2

Packaging Material: Polywrap