



Product: [9540](#)

RS232, #24-10c, SR-PVC, O/A Foil, PVC Jkt, CMG

### Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	RS-232 Applications; Computer Communications; Low Voltage Analog Signals (4-20mA, 0-10V, ...); Low Voltage Digital Control (24V, ...); Line Level Audio; Panel Wiring
------------------------	---

#### Construction Details

##### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	10	24 AWG	7x32	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	0.044 in (1.1 mm)	Black, White, Red, Green, Brown, Blue, Orange, Yellow, Purple, Gray

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.244 in (6.20 mm)

Overall Cable Diameter (Nominal): 0.244 in (6.20 mm)

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	25 Ohm/1000ft	30 pF/ft (98 pF/m)	55 pF/ft (180 pF/m)	1.5 Amps per Conductor at 25°C

##### Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
60°C (UL CMG);80°C (UL AWM 2464)	-30°C to +80°C

##### Bend Radius

Stationary Min.	Installation Min.
2.9 in (74 mm)	2.9 in (74 mm)

Max. Pull Tension:	61 lbs (28 kg)
Bulk Cable Weight:	37 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.511 Revision Date: 01-20-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC/EAN
9540.0030	Chrome	Reel	30 m	8719605022080
9540 060100	Chrome	Reel	100 ft	612825255468
9540.00U152	Chrome	UnReel	152 m	8719605022103
9540.01152	Chrome	Reel	152 m	8719605022127
9540.00305	Chrome	Reel	305 m	8719605022097
9540.00U305	Chrome	UnReel	305 m	8719605022110
9540 060500	Chrome	Reel	500 ft	612825255482
9540 060U500	Chrome	UnReel	500 ft	612825255451
9540 0601000	Chrome	Reel	1,000 ft	612825255475
9540 060U1000	Chrome	UnReel	1,000 ft	612825255444
9540 0605000	Chrome	Reel	5,000 ft	612825255499

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.