

STPS240H100TV1Y

Datasheet

Automotive 100 V, 2 x 120 A, power Schottky rectifier





ISOTOP

Product status link
STPS240H100TV1Y

Product summary		
Symbol Value		
I _{F(AV)}	2 x 120 A	
V _{RRM}	100 V	
T _j (max.)	175 °C	
V _F (typ.)	0.610 V	

Features

- AEC-Q101 qualified
- PPAP capable
- Operating T_i from -40 °C to +175 °C
- Low thermal resistance
- Negligible switching losses
- Low C_{J0}
- High forward surge capability
- Avalanche rated
 - Insulated package ISOTOP:
 - Insulated voltage: 2500 V_{RMS} sine
- ECOPACK2 compliant component
- Comply with UL1557 insulation: 2.5 kV
 - Reference file: E81734

Applications

- DC/DC converter, especially in hybrid or electrical vehicles
- OBC
- Secondary rectification
- LLC topologies
- Phase shift topologies

Description

The STPS240H100TV1Y is an automotive Schottky diode suitable for high frequency switch mode power supply.

Especially suited for DC-DC applications, this isolated ISOTOP Schottky diode will improve the thermal management in harshest environments. Its high forward surge capability ensures a good robustness during transient phases or in case of short circuit event.

1 Characteristics

(1)

Table 1. Absolute ratings (limiting values, per diode at T_{amb} = 25 °C, unless otherwise specified)

Symbol	Parameter	Value	Unit		
V _{RRM}	Repetitive peak reverse voltage, T _j = -40 °C to +175 °C		100	V	
I _{F(RMS)}	Forward rms current		225	А	
1	Average forward surrent $\delta = 0.5$, equate wave	T_C = 140 °C, per diode	120	•	
IF(AV)	Average forward current, 0 = 0.5, square wave	T _C = 140 °C, per device	240	A	
I _{FSM}	Surge non repetitive forward current	t _p = 10 ms sinusoidal	1150	А	
P _{ARM}	Repetitive peak avalanche power $t_p = 10 \ \mu s, T_j = 125 \ ^{\circ}C$		9300	W	
T _{stg}	Storage temperature range		-55 to +175	°C	
Тј	Maximum operating junction temperature ⁽¹⁾		-40 to +175	°C	

1. $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameters

Symbol	Parameter	Typ. value	Unit		
R _{th(j-c)}	Junction to case	Per diode	0.24	°C/M/	
		Total	0.12	0/11	

Table 3. Static electrical characteristics (per diode)

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
		T _j = 25 °C	V _R = 15 V	-		40	μA
I _R ⁽¹⁾	Reverse leakage current	T _j = 25 °C	V _R = V _{RRM}	-		90	
		T _j = 125 °C		-	26	65	mA
V _F ⁽²⁾ Forward volta		T _j = 25 °C	I _F = 60 A	-		0.700	V
		T _j = 150 °C		-	0.505	0.570	
	Forward voltage drop	T _j = 25 °C	I _F = 80 A	-		0.750	
	Torward voltage drop	T _j = 150 °C		-	0.545	0.610	
		T _j = 25 °C	I _F = 120 A	-		0.825	
		T _j = 150 °C		-	0.610	0.680	

1. Pulse test: $t_p = 5 ms$, $\delta < 2\%$

2. Pulse test: $t_p = 380 \ \mu s, \ \delta < 2\%$

To evaluate the maximum conduction losses, use the following equation:

 $P = 0.46 \times I_{F(AV)} + 0.00183 \times I_{F}^{2} (RMS)$

For more information, please refer to the following application notes related to the power losses :

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode



1.1 Characteristics (curves)





Figure 4. Junction capacitance versus reverse voltage applied (typical values, per diode)







10

0.001

1

t_բ(µs)

1000

100

2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 ISOTOP package information

- Epoxy meets UL94, V0
- Cooling method: by conduction (C)
- Recommended torque value: 1.3 N·m
- Maximum torque value: 1.5 N·m

STMicroelectronics strongly recommend the use of the screws delivered with this product. The use of any other screws is entirely at the user's own risk and will invalidate the warranty.

Figure 7. ISOTOP package outline



	Dimensions				
Ref.	Millim	neters	Inches ⁽¹⁾		
	Min.	Max.	Min.	Max.	
A	11.80	12.20	0.460	0.480	
A1	8.90	9.10	0.350	0.358	
В	7.80	8.20	0.307	0.323	
С	0.75	0.85	0.030	0.033	
C2	1.95	2.05	0.077	0.081	
D	37.80	38.20	1.488	1.504	
D1	31.50	31.70	1.240	1.248	
E	25.15	25.50	0.990	1.004	
E1	23.85	24.15	0.939	0.951	
E2	24	.80	0.976		
G	14.90	15.10	0.587	0.594	
G1	12.60	12.80	0.496	0.504	
G2	3.50	4.30	0.138	0.169	
F	4.10	4.30	0.161	0.169	
F1	4.60	5.00	0.181	0.197	
Н	-0.05	0.10	-0.002	0.004	
Diam P	4.00	4.30	0.157	0.169	
P1	4.00	4.40	0.157	0.173	
S	30.10	30.30	1.185	1.193	

Table 4. ISOTOP package mechanical data

1. Inches given for reference only

For more information, please refer to the following technical note related to the mouting :

TN1331: Assembly recommendations for STMicroelectronics ISOTOP package



3 Ordering Information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS240H100TV1Y	STPS 240H100TV1Y	ISOTOP	27 g without screws	10 with screws	Tube

Table 5. Ordering information

Revision history

Date	Version	Changes
18-Feb-2020	1	First issue.
05-May-2020	2	Updated Table 1. Added Mounting information.
08-Jun-2020	3	Updated Figure 3 and inserted TN1331 reference.
12-Jun-2020	Λ	Removed section 3 Mounting information.
	4	Minor text changes to improve the readibility.

Table 6. Document revision history

IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics – All rights reserved