

End mill HSSE Co 5

6 flutes, uncoated

ORION[®]

Application:

End mill for universal machining.

Execution:

- HSSE Co 5
- With Morse taper and internal draw-in thread (from Morse taper 4 with collar and driving surface in accordance with DIN 2207).
- Type N
- Finishing teeth
- Twist angle 30°



Art. no.	15350 160
Brand	ORION
Manufacturer Part Number	15350160
Cutting material	HSSE Co5
Surface	Uncoated
Type	N
Number of cutting edges	4 PCS
Twist angle	30°
Edge protection chamfer length	0.2 mm
Tool holding device	Morse taper shank
Construction length	Normal
Cutting edge diameter	16 mm
Cutting edge length	32 mm
Length	117 mm
Morse taper size	MK 2
Female thread	10 mm
fz steel 700	0.05 mm
Gross Weight	0.146 kg
Product Group	106

EAN

4039247095865