

Hydro-expansion chuck type A

Short slimline design

ATORN[®]

Application

For clamping drill bits and milling tools with straight shank.

Version

- High clamping forces
- With axial length adjustment (max. V in the drawing)
- Highly precise centric clamping
- Outstanding absorption
- Standard tool changes as with expansion chucks without requiring additional devices
- Various applications when used with reducer bushings
- With Balluff chip hole
- Can be clamped with all common shank types

Advantage

- High degree of torque transmission
- Good surface qualities
- Suitable for high rotation speeds
- Excellent vibration-absorbing properties
- Longer service life of cutting tools

Delivery

Tool holder with matching hex key



| | |
|-------------------------------|------------------|
| Art. no. | 23733 151 |
| Tool holding device | HSK 100 |
| Overall length | Short-slim |
| Clamping diameter | 8 mm |
| Form | A |
| Projecting length | 75 mm |
| Outer diameter | 50 mm |
| Clamp in depth | 37 mm |
| Suitable for thread | M6 |
| Width across flats | 5 mm |
| Max. adjustment travel | 10 mm |
| Coolant supply | Internal |
| Balancing quality | G 2.5 at 25 rpm |

EAN-Code

4050293151503

