

SXE 150-5.0 BL random orbital sander

350 W, 5 mm oscillating circuit

metabo[®]

Application:

for finishing surfaces.

Version:

- extremely lightweight and flat random orbital sander with symmetrical design for easy change of hands or two-handed operation
- non-slip paddle switch with dead-man function for safe starting and optional speed control
- electronic pre-setting of the desired speed range
- motor and disc brake allow the machine to be put down quickly
- separate main switch protects against unintentional start
- grinding plate with multi-hole pattern for effective extraction and longer life of abrasive
- easy to service thanks to removable cable

Delivery:

„multi-hole“ grinding plate with hook and loop fastening, open-end spanner, in case



Art. no.	70535 255
Model	SXE 150-5 BL
Manufacturer Article Number	615050700
Support-disc diameter	150 mm
Min./max. idle speed	4000-10000 rpm
Power input	350 W
Oscillating diameter	5 mm
Weight	1 kg
With rubber-coated handle	Yes
With electronic feedback	Yes
With soft start	Yes
With dead man function	Yes
Cable length	4.3 m

EAN-Code

4007430320810