

Key Features

- Nylon toggle switches
- Ratings up to 20A, 250V ac
- Single and double pole
- Wide choice of terminals
- Choice of circuit options including 3 position
- Flat & round actuator options

Approvals and specifications


- ☑ 16(4)A 250Vac T85
 - ☑ UL 20A 250Vac Non Ind (Single pole)
 - ☑ UL 16A 250Vac Non Ind (Double pole)
 - ☑ UL CSA (2 pos types) 250Vac 1hp, 125Vac 1/2hp
 - ☑ UL CSA (3 pos types) 250Vac 1/2hp, 125Vac 1/4hp
 - ☑ CSA 16A 250Vac Non Ind
 - ☑ UL 85°C, file E45221, CSA file LR10990
 - ☑ UL and CSA N/A on momentary types
- Selective "A, B, C" and "OFF, A, A+B" circuits at 5 amp also available.
3mm contact gap except where marked μ .

Terminal	Function	Actuator	Body	Options
<p>C</p>	<p>Single Pole</p> <p>1700 ON - OFF</p>	<p>H</p>	<p>O Single pole</p> <p>Thread: 15/32" x 32TPI</p>	<p>Neck Seal M539</p> <p>Material - Nitrile (H & R Actuators) Actuator visible</p>
<p>H</p>	<p>Double Pole</p> <p>1750 ON - OFF</p>	<p>R</p>	<p>O Double Pole</p> <p>Thread: 15/32" x 32TPI</p> <p>Panel hole (all types) Panel thickness (Max) Both nuts - 3.5mm Less backnut - 6.5mm</p>	<p>Cover M1080</p> <p>Material - EPDM (R Actuator only)</p>
<p>K</p>	<p>1710 μ ON - ON</p>			<p>Cover M531</p> <p>Material - PVC (R Actuator only)</p>
<p>T</p>	<p>1720 μ ON - OFF - ON</p>			<p>Fixing nuts (Standard is M506 & T92)</p> <p>T5 Hex brass M506 Hex nylon</p>
<p>X</p>	<p>1721 μ ON - OFF - ON μ (momentary 1 side)</p>			<p>T92 Knurled brass - slotted</p>
	<p>1722 ON - OFF - ON μ (momentary 2 sides)</p>	<p>The switch is on between centre terminals (2 & 5) and the terminals over which the lever is positioned.</p>		<p>M279 Knurled nylon</p>
				<p>Plate P236 Plate SP or DP</p>

Dimensions mm) * Indicates ON position (for ON - OFF switches)

Single pole


(C terminals shown)




Optional
F00232PAAA
plate SP or DP

Double pole


(C terminals shown)



Without barrier



With barrier



Examples



C1700R --



C1700H --



C1760R --



C1750H --