

## 3-point internal micrometer

**ORION**<sup>®</sup>

### Application:

For measuring through-bores and short centring shoulders.

### Execution:

- Scale with anti-glare, brushed chromium plated finish
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force

### Delivery:

Single device with setting ring and measuring depth extension in a case



<b>Art. no.</b>	<b>31910 010</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	31910010
<b>Min./max. length measuring range</b>	10-12 mm
<b>Measuring depth</b>	54 mm
<b>Error limit</b>	4 µm
<b>Vernier scale</b>	0.005 mm
<b>Extensions provided</b>	100 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Adjusting ring diameter</b>	10 mm
<b>Calibration Group</b>	I, AC
<b>DIN</b>	863
<b>Calibration Group Description</b>	Internal micrometers (3 point)
<b>Gross Weight</b>	0.600 kg
<b>Product Group</b>	3BB

### EAN

4039247459476