

**Model Number**


**V1-G-BK0,6M-PUR-U-TV1-G**

Y connecting cable, M12 to 2xM12, 4-pin, PUR cable

**Features**

- Simple assembling of 2 signals to one M12 plug-in station
- Immunity to vibration, with mechanical latching
- Suitable for drag chains
- Suitable for robotic applications / torsion resistant
- Flame resistant cable
- Halogen-free
- Resistant to microbes and hydrolysis
- Free of paint coating substances

**Dimensions**



**Technical data**

**General specifications**

Number of pins 4

**Electrical specifications**

Operating voltage  $U_B$  max. 30 V AC/DC

Operating current  $I_B$  max. 4 A

Volume resistance  $\leq 5 \text{ m}\Omega$

Surge protection overvoltage category III

**Ambient conditions**

Ambient temperature Body: -40 ... 90 °C (-40 ... 194 °F)  
cable, fixed: -40 ... 80 °C (-40 ... 176 °F)  
cable, flexing: -25 ... 80 °C (-13 ... 176 °F)

Pollution degree 3

**Mechanical specifications**

Contact elements spring-loaded contact socket

Pin diameter 1 mm

Degree of protection IP67

Connection 1 x M12 connector, straight  
2 x M12 straight sockets

**Material**

Contacts CuSn / Au

Contact surface Au

Body TPU, black

Cable PUR

Slotted nut Diecast zinc

Sleeve connector Diecast zinc

Core insulation PP

Cable extra-fine wire, flexible

Sheath diameter  $\varnothing 4.3 \text{ mm}$

Bending radius  $> 10 \times$  cable diameter, moving  
 $> 5 \times$  cable diameter, fixed

Color black

Cores  $4 \times 0.34 \text{ mm}^2$

Conductor construction  $42 \times 0.1 \text{ mm } \varnothing$

Length L  $L_1 = 0.6 \text{ m}$   
 $L_2 = 0.6 \text{ m}$

**Drag chain suitability**

Drag chain cycles  $\geq 5000000$  (at max. 60 °C)

Motion velocity  $\leq 3.3 \text{ m/s}$

Traverse distance 5 m horizontal

Acceleration  $\leq 5 \text{ m/s}^2$


Torsion cycles  $\geq 1000000$  (at max. 60 °C)

Torsional stress  $\pm 180 \text{ }^\circ/\text{m}$

**Flammability**

Contact carrier 94 HB

**Electrical connection**



Release date: 2016-05-18 10:02 Date of issue: 2016-05-18 252972\_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**pepperl+fuchs**  
SENSING YOUR NEEDS

|   |  |
|---|--|
| Housing   | 94 V-2                                 |
| Cable   | FT2                                    |
| <b>Compliance with standards and directives</b> |  |
| Standard conformity                             |  |
| Degree of protection                            | EN 60529:2000                          |
| Standards                                       | IEC 61076-2-101:2008                   |
| Flammability                                    | Grip: UL 94<br>Cable: UL 758 / UL 1581 |
| Halogen-free                                    | IEC 60754-1:1994/DIN VDE 0472-815      |

Release date: 2016-05-18 10:02 Date of issue: 2016-05-18 252972\_eng.xml