

TUIJA-3-W

~55° wide beam


TECHNICAL SPECIFICATIONS:

Dimensions	Ø 50.0 mm
Height	14.5 mm
Fastening	glue, pin
Colour	clear
Box size	480 x 280 x 300 mm
Box weight	6.4 kg
Quantity in Box	364 pcs
ROHS compliant	yes ⓘ



MATERIAL SPECIFICATIONS:



Component	Type	Material	Colour
TUIJA-3-W	Multi-lens	PMMA	clear




PHOTOMETRIC DATA (MEASURED):




LED XB-D
 FWHM 50.0°
 Efficiency 92 %
 Peak intensity 1.200 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED XB-D
 FWHM 49.0°
 Efficiency 86 %
 Peak intensity 1.100 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED XP-E
 FWHM 58.0°
 Efficiency 86 %
 Peak intensity 0.920 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED XP-G
 FWHM 59.0°
 Efficiency 86 %
 Peak intensity 0.750 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):

LUMILEDS

LED LUXEON A
FWHM 56.0°
Efficiency 86 %
Peak intensity cd/lm
LEDs/each optic 1
Light colour White
Required components:

LUMILEDS

LED LUXEON Rebel
FWHM 48.0°
Efficiency 86 %
Peak intensity 1.100 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LUMILEDS

LED LUXEON Rebel ES
FWHM 56.0°
Efficiency 86 %
Peak intensity 0.870 cd/lm
LEDs/each optic 1
Light colour White
Required components:

OSRAM Opto Semiconductors

LED OSOLON SSL 80
FWHM 46.0°
Efficiency 86 %
Peak intensity 0.440 cd/lm
LEDs/each optic 1
Light colour White
Required components:


PHOTOMETRIC DATA (MEASURED):

 SEOUL SEMICONDUCTOR		
LED	Z5	
FWHM	48.0°	
Efficiency	88 %	
Peak intensity	1.400 cd/lm	
LEDs/each optic	1	
Light colour	White	
Required components:		
SHARP		
LED	Double Dome (GM2BB)	
FWHM	58.0°	
Efficiency	86 %	
Peak intensity	cd/lm	
LEDs/each optic	1	
Light colour	White	
Required components:		

PHOTOMETRIC DATA (SIMULATED):



LED XT-E
FWHM 56.0°
Efficiency 93 %
Peak intensity 1.173 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED NCSxx19A
FWHM 54.0°
Efficiency %
Peak intensity cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED NVSxx19A
FWHM 54.0°
Efficiency %
Peak intensity cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED OSLOM SSL 150
FWHM 58.0°
Efficiency %
Peak intensity 1.100 cd/lm
LEDs/each optic 1
Light colour White
Required components:

PHOTOMETRIC DATA (SIMULATED):


OSRAM
Opto Semiconductors

LED SFH 4715AS
FWHM 48.0°
Efficiency 94 %
Peak intensity 1.440 cd/lm
LEDs/each optic 1
Light colour IR
Required components:




OSRAM
Opto Semiconductors

LED SFH 4716AS
FWHM 56.0°
Efficiency 94 %
Peak intensity 1.120 cd/lm
LEDs/each optic 1
Light colour IR
Required components:



OSRAM
Opto Semiconductors

LED SFH 4725S
FWHM 51.0°
Efficiency 94 %
Peak intensity 1.400 cd/lm
LEDs/each optic 1
Light colour IR
Required components:



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)