Report Date: 21/04/2006 1 / 5

REVISION DATE: 12-04-2006 SDS No.: 10504



SAFETY DATA SHEET RONSEAL KITCHEN AND BATHROOM TOUCH-UP ENAMEL

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND COMPANY/ UNDERTAKING

PRODUCT NAME RONSEAL KITCHEN AND BATHROOM TOUCH-UP ENAMEL

PRODUCT NO. 23160

INTERNAL ID (Commodity Code 320890 91 00)

SYNONYMS, TRADE NAMES (SPN 10504)

APPLICATION Decorative coating

SUPPLIER Ronseal Ltd

Thorncliffe Park Chapeltown Sheffield S35 2YP enquiry@ronseal.co.uk

EMERGENCY TELEPHONE Tel +44 (0) 114 246 7171

Fax +44 (0) 114 245 5629

2 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
BUTANONE	201-159-0	78-93-3	10-25%	F;R11 Xi;R36 R66 R67
BUTYL ACETATE -norm	204-658-1	123-86-4	10-25%	R10 R66 R67
PROPAN-2-OL	200-661-7	67-63-0	2.5-10%	F;R11 Xi;R36 R67
TITANIUM DIOXIDE		13463-67-7	10-25%	-
XYLENE	215-535-7	1330-20-7	10-25%	R10 Xn;R20/21 Xi;R38

The Full Text for all R-Phrases are Displayed in Section 16

COMPOSITION COMMENTS

EU VOC limit value for this product (cat A/i): 600g/l (2007) / 500g/l (2010).

3 HAZARDS IDENTIFICATION

Highly flammable. Harmful by inhalation and in contact with skin. Repeated exposure may cause skin dryness or cracking.

CLASSIFICATION Xn;R20/21. F;R11. R66.

4 FIRST-AID MEASURES

GENERAL INFORMATION

In all cases of doubt, or when symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person.

INHALATION

Remove to fresh air, keep the patient warm and at rest. If breathing has stopped administer artificial respiration. Give nothing by mouth. If unconscious, place in the recovery position and seek medical advice.

INGESTION

If accidentally swallowed obtain immediate medical attention. Keep at rest. Do NOT induce vomiting.

SKIN CONTACT

Remove contaminated clothing. Wash skin thoroughly with soap and water, or use a proprietary skin cleanser. Do NOT use solvents or thinners. Seek medical advice if any irritation persists.

Report Date: 21/04/2006 2 / 5

REVISION DATE: 12-04-2006 SDS No.: 10504

RONSEAL KITCHEN AND BATHROOM TOUCH-UP ENAMEL

EYE CONTACT

Contact lenses should be removed. Irrigate copiously with clean, fresh water for at least 10 minutes, holding the eyelids apart, and seek medical advice.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Fire can be extinguished using: alcohol resistant foam, carbon dioxide (CO2), powder, water spray/ mist. Do not use water jet.

SPECIAL FIRE FIGHTING PROCEDURES

Fire will produce dense black smoke containing hazardous products of combustion (see Section 10). Exposure to decomposition products may be hazardous to health. Appropriate self-contained breathing apparatus may be required. Cool closed containers exposed to fire with water spray. Do not allow run-off from fire fighting to enter drains or watercourses.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Exclude sources of ignition and ventilate the area. Exclude non-essential personnel. Avoid breathing vapours. Refer to protective measures listed in Section 7 and 8. Contain and collect spillage with non-combustible absorbent materials, e.g. sand, earth or vermiculite, and place in a suitable container for disposal in accordance with the waste regulations (see Section 13). Clean preferably with a detergent; avoid the use of solvents. If the product enters drains or sewers, immediately contact the local water company; in the case of contamination of streams, rivers or lakes, the relevant environment agency.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Keep away from heat, sparks and open flame. Vapours are heavier than air and may spread along floors. They may form explosive mixtures with air. Prevent the creation of flammable or explosive concentrations of vapour in air and avoid vapour concentrations higher than the occupational exposure limits. Smoking, eating and drinking should be prohibited in areas of storage and use. Prevent airborne concentrations higher than the occupational exposure limits. Provide good ventilation. Avoid inhalation of vapours. Avoid inhalation of dust.

Where possible, wet flatting methods or chemical strippers should be used to avoid the creation of dust. For Occupational Exposure Controls, refer to Section 8.

The Manual Handling Operations Regulations may apply to the handling of containers/packages of this product.

STORAGE PRECAUTIONS

Keep containers tightly closed. Observe the label precautions. Store between 5°C and 25°C. Keep in a cool, dry, well ventilated place, away from sources of heat, ignition and direct sunlight. No smoking.

The principles contained in the HSE Guidance Note: Storage of Packaged Dangerous Substances, should be observed when storing this product.

To avoid the risk of spillage, always store and transport in a secure and upright position.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	LT - ppm	LT - mg/m3	ST - ppm	ST - mg/m3
XYLENE	WEL	50 ppm(Sk)	220 mg/m3(Sk)	100 ppm(Sk)	441 mg/m3(Sk)
PROPAN-2-OL	WEL	400 ppm	999 mg/m3	500 ppm	1250 mg/m3
BUTANONE	IOELV	200 ppm(Sk)	600 mg/m3(Sk)	300 ppm(Sk)	899 mg/m3(Sk)
BUTYL ACETATE -norm	WEL	150 ppm	724 mg/m3	200 ppm	966 mg/m3
TITANIUM DIOXIDE	WEL		4 mg/m3 resp. dust		

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits SUP = Supplier's recommendation.

ENGINEERING MEASURES

Provide adequate ventilation. Where reasonably practicable, this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and/or solvent vapours below the relevant occupational exposure limits, suitable respiratory protective equipment should be worn.

RESPIRATORY EQUIPMENT

If exposure to hazardous substances identified above cannot be controlled by the provision of local exhaust ventilation and good general extraction, suitable respiratory protective equipment should be worn.

Report Date : 21/04/2006 3 / 5

REVISION DATE: 12-04-2006 SDS No.: 10504

RONSEAL KITCHEN AND BATHROOM TOUCH-UP ENAMEL

HAND PROTECTION

When skin exposure may occur, advice should be sought from glove suppliers on appropriate types. Barrier creams may help to protect exposed areas of skin but are not substitutes for full physical protection. They should not be applied once exposure has occurred.

EYE PROTECTION

Eye protection designed to protect against liquid splashes should be worn.

OTHER PROTECTION

Cotton or cotton/synthetic overalls or coveralls are normally suitable. Grossly contaminated clothing should be removed and the skin washed with soap and water or a proprietary skin cleaner. Do not use solvents or thinners as skin cleaning agents.

All personal protective equipment, including respiratory protective equipment, used to control exposure to hazardous substances must be selected to meet the requirements of the COSHH Regulations.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE Screw cap container with integral brush, containing a flammable liquid.

COLOUR White

ODOUR Characteristic solvent type.

SOLUBILITY Immiscible with water

RELATIVE DENSITY 1.05 - 1.15 VAPOUR DENSITY (air=1) >1

FLASH POINT (°C) Less than 23 CC (Closed VOLATILE ORGANIC COMPOUND (530 g/litre

cup). VOC)

10 STABILITY AND REACTIVITY

STABILITY

Stable if stored under recommended storage and handling conditions.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition.

HAZARDOUS DECOMPOSITION PRODUCTS

In a fire, hazardous decomposition products such as smoke, carbon monoxide, carbon dioxide and oxides of nitrogen may be produced.

11 TOXICOLOGICAL INFORMATION

TOXICOLOGICAL INFORMATION

There is no data available on the product itself. The product has been assessed following the conventional method in CHIP and is classified for toxicological hazards accordingly. This takes into account, where known, delayed and immediate effects and also chronic effects from components from short-term and long-term exposure by oral, inhalation and dermal routes of exposure and eye contact. See Sections 3 and 15 for details of the resulting hazard classification.

Exposure to organic solvent vapours in excess of the stated occupational exposure limit may result in adverse health effects such as irritation of the mucous membrane and the respiratory system and adverse effects on the kidney, liver and central nervous systems. Symptoms and signs include headache, dizziness, fatigue, muscular weakness, drowsiness and in extreme cases loss of consciousness.

Solvents may cause some of the above effects by absorption through the skin.

Repeated or prolonged contact with the product may lead to removal of natural fats from the skin resulting in non-allergic contact dermatitis and absorption through the skin. Splashes in the eyes may cause irritation and reversible local damage.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

The product has been assessed following the conventional method in CHIP and is classified for ecological hazards accordingly. See Sections 3 and 15 for details.

DEGRADABILITY

There is no data available on the product itself.

Report Date : 21/04/2006 4 / 5

REVISION DATE: 12-04-2006 SDS No.: 10504

RONSEAL KITCHEN AND BATHROOM TOUCH-UP ENAMEL

ACUTE FISH TOXICITY

There is no data available on the product itself.

WATER HAZARD CLASSIFICATION

There is no data available on the product itself. The product should not be allowed to enter drains or watercourses, or be deposited where it can affect ground or surface waters.

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Do not allow into drains or watercourses, or dispose of where ground or surface waters may be affected. Wastes, including emptied containers, are controlled wastes and should be disposed of in accordance with regulations made under the Control of Pollution Act and the Environmental Protection Act. Using information provided in this data sheet, advice should be obtained from the relevant waste authority on the classification of empty containers.

14 TRANSPORT INFORMATION

GENERAL

Transport within user's premises: always transport in closed containers that are upright and secure. Ensure that person's transporting the product know what to do in an accident or spillage.

Limited Quantity concessions may apply to the carriage of this product.



PROPER SHIPPING NAME PAINT

UN NO. ROAD 1263 ADR CLASS Class 3: Flammable liquids.

 ADR PACK GROUP
 II
 UN NO. SEA
 1263

 IMDG CLASS
 3
 IMDG PACK GR.
 II

 EMS
 F-E; S-E
 MARINE POLLUTANT
 No.

15 REGULATORY INFORMATION

LABELLING



Harmful



Highly Flammable

CONTAINS XYLENE

RISK PHRASES

R11 Highly flammable.

R20/21 Harmful by inhalation and in contact with skin.

R66 Repeated exposure may cause skin dryness or cracking.

SAFETY PHRASES

S2 Keep out of the reach of children

S16 Keep away from sources of ignition - No smoking.

S37 Wear suitable gloves.

S46 If swallowed, seek medical advice immediately and show this container or

label.

S51 Use only in well-ventilated areas.

UK REGULATORY REFERENCES

The product is classified and labelled for supply in accordance with the Chemicals (Hazard Information and Packaging for Supply) Regulations [CHIP]

Report Date : 21/04/2006 5 / 5

REVISION DATE: 12-04-2006 SDS No.: 10504

RONSEAL KITCHEN AND BATHROOM TOUCH-UP ENAMEL

The information contained in this safety data sheet does not constitute the user's own assessment of workplace risks as required by other health and safety legislation.

The provisions of the Health and Safety at Work etc. Act and the Control of Substances Hazardous to Health Regulations apply to the use of this product at work.

The Manual Handling Operations Regulations

The Chemicals (Hazard Information and Packaging for Supply) Regulations.

The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations.

European Agreement concerning the International Carriage of Dangerous Goods by Road [ADR]

EU DIRECTIVES

Dangerous Substance Directive 67/548 Dangerous Preparations Directive 88/379 Safety Data Sheet Directive 91/155 VOC Directive 2004/42/CE

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION

GENERAL INFORMATION

The information contained in this safety data sheet is based on the present state of knowledge and current national legislation. It provides guidance on health, safety and environmental aspects of the product and should not be construed as any guarantee of technical performance or suitability for particular applications.

The product should not be used for purposes other than those shown in section 1 without first referring to the supplier and obtaining written handling instructions. As the specific conditions of use of the product are outside the supplier's control, the user is responsible for ensuring that the requirements of relevant legislation are complied with.

For specific guidance contact Ronseal Technical Services. [Helpline +44 (0) 114 240 9469] ; Email: enquiry@ronseal.co. uk

REVISION COMMENTS

Formulation change. Implementation of EH40/2005: Workplace Exposure Limits (WELs) Revised Transport Information.

REV. NO./REPL. SDS 10504/1
GENERATED 12-04-2006

SDS NO. 10504/2

SAFETY DATA SHEET STATUS

Approved.

DATE 12-04-2006
SIGNATURE K. R. P. Winder.

RISK PHRASES IN FULL

R10 Flammable. R11 Highly flammable.

R20/21 Harmful by inhalation and in contact with skin.

R36 Irritating to eyes.
R38 Irritating to skin.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

DISCLAIMER

Information contained in this Safety Data Sheet is based on data considered to be accurate at the time of its preparation. Despite our efforts, it may not be up to date or applicable to the circumstances of any particular case.

The supplier accepts no responsibility whatsoever (except otherwise provided in law) for any damage or injury resulting from abnormal use, from any failure to follow appropriate practices or from hazards inherent in the product.