

Product Data

Optigear Synthetic PD...ES Range

High Performance Synthetic Gear Oil

Description

Castrol OptigearTM Synthetic PD...ES Range is based on synthetic hydrocarbons (PAO) with Castrol's advanced gear oil system which gives special plastic deformation (PD) and surface improvement performance. The additive package, when activated by high specific loads and corresponding temperatures, helps to equalize surface roughness without creating abrasion leading to the surface improvement (plastic deformation).

Optigear Synthetic PD...ES is a CLP-HC gear oil (according to DIN 51502) and exceeds the minimum requirements according to DIN 51517, part 3, CLP gear oils and is formulated with detergent type additives.

Optigear Synthetic PD 150 ES to PD 460 ES gear oils are approved by Flender (Flender gear units - Listing T 7300, Rev. 16, formerly Siemens Mechanical Drives).

Application

Optigear Synthetic PD...ES may be used in spur gear, bevel gears or planetary gear units and in heavy loaded gear units. It is also suitable for the lubrication of oil-lubricated rolling bearings. It is especially designed to reduce friction losses and can reduce energy consumption compared to more conventional lubricants. The lower friction observed with Optigear Synthetic PD...ES means less stress in the contact point subsurface area, which means lower risk for pittings and micropittings.

Being synthetic based it will also withstand higher temperatures and provide extended life. Depending on the specific application, Optigear Synthetic PD...ES may be used in an operating temperature range from -40°C to +100°C, and upto +120°C for short periods. (Note the lower operating temperature is dependent on the pour point).

The beneficial effects of the special PD additives contained in Optigear Synthetic PD...ES will be reduced if mixed with other lubricants. If mixing with other oils cannot be avoided, contact our local technical support team for advice on compatibility (as a guide at least <5% of other oils is preferred). Optigear Synthetic PD...ES is compatible with most commonly used elastomer seal materials.

Advantages

- High load carrying capacity
- Very low friction coefficient and frictional torque
- Superior micropitting protection
- Surface smoothing effect
- Excellent bearing lubrication suitability
- Good filtration properties
- Long life lubricant

Typical Characteristics

| | | I | 1 | 1 | 1 | 1 | 1 | | 1 |
|---|----------------------------|--|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|
| Name | Method | Units | PD 68 ES | PD 100 ES | PD 150 ES | PD 220 ES | PD 320 ES | PD 460 ES | PD 680 ES |
| Appearance | Visual | - | Clear & Bright |
| ISO Viscosity Grade | - | - | 68 | 100 | 150 | 220 | 320 | 460 | 680 |
| Density @ 15°C / 59°F | ISO 12185 / ASTM D4052 | kg/m³ | 846 | 849 | 851 | 853 | 855 | 858 | 860 |
| Kinematic Viscosity @ 40°C / 104°F | ISO 3104 / ASTM D445 | mm²/s | 71.5 | 105 | 158 | 230 | 330 | 460 | 670 |
| Kinematic Viscosity @ 100°C / 212°F | ISO 3104 / ASTM D445 | mm²/s | 11.3 | 15.7 | 22.1 | 30.2 | 40.7 | 50.5 | 64.2 |
| Viscosity Index | ISO 2909 / ASTM D2270 | - | 151 | 159 | 167 | 172 | 177 | 172 | 167 |
| Flash Point - open cup method | ISO 2592 / ASTM D92 | °C °F | >250 >482 |
| Copper corrosion (3 h @ 100°C/212°F) | ISO 2160 / ASTM D130 | Rating | 1 | 1 | 1 | 1 | 1 | 1 | 1 |
| Rust test - synthetic seawater (24 h) | ISO 7120 / ASTM D665B | Rating | Pass |
| Foam, Sequences I/II/III tendency / stability | ISO 6247 / ASTM D892 | ml/ml | 0/0 | 0/0 | 0/0 | 0/0 | 0/0 | 0/0 | 0/0 |
| Pour Point | ISO 3016 / ASTM D97 | °C °F | -51 -60 | -51 -60 | -51 -60 | -48 -54 | -45 -49 | -42 -44 | -36 -33 |
| Oxidation Stability (312 hrs @ 121°C) | ISO 4263-4 / ASTM D2893 | Viscosity increase @ 100°C (%) | 0.8 | 0.8 | 0.9 | 1.0 | 1.0 | 1.5 | 3.5 |
| Elastomer Compatibility - with NBR 28, 168 hours @100°C | ISO 1817 | - | Pass |
| FZG Gear Scuffing test A/8.3/90 | ISO 14635-1 | Failure Load Stage | >12 | >12* | >12 | >14 | >14 | >14* | >14* |
| FZG Micropitting test @ 90°C/194°F | FVA 54-7 | Failure Load Stage Micropitting Rating | - | - | >10 high | >10* high* | >10* high* | >10* high* | >10* high* |
| FE8 Bearing Wear test (F.562831.01-7.5/80-80) | DIN 51819-3 | Roller wear (Mw ₅₀), mg | <5 | <5* | <5 | <5* | <5* | <5* | <5* |

Subject to usual manufacturing tolerances. *Read across from lower viscosity.

Optigear Synthetic PD...ES Range

07 Nov 2018

Castrol, the Castrol logo and related marks are trademarks of Castrol Limited, used under licence.

This data sheet and the information it contains is believed to be accurate as of the date of printing. However, no warranty or representation, express or implied, is made as to its accuracy or completeness. Data provided is based on standard tests under laboratory conditions and is given as a guide only. Users are advised to ensure that they refer to the latest version of this data sheet. It is the responsibility of the user to evaluate and use products safely, to assess suitability for the intended application and to comply with all applicable laws and regulations. Material Safety Data Sheets are available for all our products and should be consulted for appropriate information regarding storage, safe handling, and disposal of the product. No responsibility is taken by either BP plc or its subsidiaries for any damage or injury resulting from abnormal use of the material. All products, services and information supplied are provided under our standard conditions of sale. You should consult our local representative if you require any further information.

 $Castrol\ Industrial, Technology\ Centre\ ,\ Whitchurch\ Hill\ ,\ Pangbourne\ ,\ Reading\ ,\ RG8\ 7QR\ ,\ United\ Kingdom$

http://msdspds.castrol.com