




ELECTRICAL TEST:

- 1.100% OPEN SHORT MIS WIRE TEST
- 2.CONTACT RESISTANCE:5 OHM MAX
- 3.INSULATION RESISTANCE:5M OHM MIN
- 4.HI-POT TEST:DC 300V/10ms
- 5.PASS 8K@60Hz TEST

| CONSUMER ITEM | LENGTH(mm) |
|---------------|------------|
| 1M | 1000±30 |
| 1.5M | 1500±30 |
| 2M | 2000±30 |



PIN Assignment



| ⑥ | CABLE | (1/0.254BC*1P+D1/0.254TC+AL-Foil+ADHESIVE-PET)*5C+1/0.254BC*4C+AL-Foil+D7/0.16TC+144#/0.12AL BLACK PVC Jacket OD:6.3±0.15mm | m |
|-----|-------------|--|------|
| ⑤ | MODEL | BLACK 45P PVC molding | xxg |
| ④ | SHELL | Silver white aluminum shell | 2PCS |
| ③ | MODEL | PE,Nature color | xxg |
| ② | Copper foil | Copper foil size:5mm | cm |
| ① | plug | HDMI AM 19P SHELL/PIN:Gold plated & Tinplate | 2pcs |
| NO. | PART NAME | DESCRIPTION | UNIT |

| | | | | DESCRIPTION | FINISHED PRODUCT'S FIGURE | SCALE | FIT | UNITS: MM | 1RD ANGLE |
|----------|---------|---------|----------|-------------|---------------------------|-------|------------|-----------|-----------|
| | | | | MODEL NO. | | △ | | | |
| APPROVED | CHECKED | DRAWING | DESIGNED | DRAWING NO. | | △ | 2021/07/09 | | A1 |
| | | | | FINISHING | | △ | 2021/06/10 | | A1 |
| | | | | MATERIAL | | SYM | DATE | | REVISION |