

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS			DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398							
DCP #	REV	DESCRIPTION		DATE	CHECKD DATE		APPRVD	DATE		
XX	Α	RELEASED		26-07-08	JN	26-07-08	JN	26-07-08		
2067	В	Listing Info Updated	JN	08-25-09	JN	08-25-09	JN	08-25-09		


#### Material

Frame : DIE-CAST ALUMINUM

Impeller : Thermoplastic PBT of UL 94V-0

Lead Wire: UL3266, 24awg, GRAY

## **DIMENSIONS**



Air Flow Direction: Toward Label side.



ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.


TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
LG	26-07-08
CHECKED BY:	DATE:
JN	26-07-08
APPROVED BY:	DATE:
JN	26-07-08

DRAW	ING TITLE:								
			Axial A	C Fa	n				
SIZE	DWG. NO.	NO.			ELECTRONIC FILE REV				
Α		MC1	9696	70	OK8579.	dwg	В		
SCALE: NTS			U.O.M.: INCHES [mm]		SHEET:	1 01	- 4		

# PERFORMANCE CURVES

#### STATIC PRESSURE





AI AI	ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART C	HOLE OR IN PART CAN BE REPRODUCED WITHOUT THE		DWG. NO.	E	ELECTRONIC FILE		REV
	EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.	on be hernosoes united the	Α	MC1	9696	70K8579		
	SPC-F005.DWG DOC. NO. SPC-F005 *	Effective: 7/8/02 * DCP No: 1398	SCALE:	NTS	U.O.M.: Millimeters	SHEET: 2	. OF 4	4

## **SPECIFICATIONS**

1-1. Rated Voltage : 115 VAC 50/60 Hz

1-2. Operating Voltage Range : 85-125 VAC

1-3. Starting Voltage : 85 VAC (25deg.C PDWER DN/DFF)

1-4 Rated Speed : 2200/2000 RPM ± 10%

1-5. Air Delivery : 76/70 CFM

1-6. Static Pressure : 0.12/0.08 Inch-HDO

1-7. Rated Current : 0.11/0.13 AMP 1-8. Rated Power : 11/11 WATTS 1-9. Noise Level : 38/36 dB(A)

1-10. Direction of Rotation : Counter-clockwise viewed from front of fan blade

1-11. Operating Temperature : -10 to +70 deg. C 1-12. Storage Temperature : -40 to +70 deg. C

1-13. Bearing System : Lubricated sleeve bearing system

1-14. Weight : 550g

1-15. Safety : UL/CUR Approvals

1-16. Vibration : Vibration of acceleration 1.5G and frequency 5~50~5Hz is applied in the

3 directions(X,Y,Z), in cycles of 1 minute each,

for a total vibration time of 30 minutes.



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER	IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE	SIZE	DWG. NO.	E	LECTRONIC FILE	LE RE		
EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.	MINOLE ON MATTHEW SAME BE THE ROBBOOLD MINIOUS THE	Α	MC1	9696	70K8579			
SPC-F005.DWG	DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398	SCALE	E: NTS	U.O.M.: Millimeters	SHEET:	3 OF	4	

## **CHARACTERISTIC**

1. Motor Design : Reliable shaded-Pole Motor Construction.

2. Insulation Resistance : 500Megohms minimum at 500 VDC.

3. Dielectric Strength : 1800 VAC for one second.

4. Motor Protection : Impedance Protected.

5. Noise Level : Measured in a semi-anechoic chamber

with background noise level below 15

dB(A).The fan is running in free air with

microphone at a distance of one meter

from the fan intake.

6. Tolerances :  $\pm 15\%$  on rated power and current.

7. Air Performance : Measured by a double chamber. The values

are recorded when the fan speed has stabilized

at rated voltage.



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER I	N WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE	SIZE	DWG. NO.		ELECTRONIC F	ILE	REV	
EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.		A	MC	19696	70K85	79		
SPC-F005.DWG	DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398	SCALE	E: NTS	U.O.M.: Millimeters	SHEET:	4 OF	F 4	