

G FUSE LINK DIN 41660 QUICK-RESPONSE HIGH  
BREAKING CAPACITY RATED UNINT. CURRENT  
1.6A




Figure similar

### Model

product brand name		SENTRON
Product designation		G fuse link
<b>Design of the product</b>		quick-response (F)
<b>Type of miniature fuse</b>		glass fuse

### General technical data

<b>Size of the fuse link</b>		5x25 mm
<b>Melting characteristics</b>		quick acting (F)

### Main circuit

Operating voltage / Rated value	V	250
Operating current / Rated value	A	1.6

### Display and operation

<b>Product component / visual fault warning</b>		No
---	--	----

<b>General Product Approval</b>	<b>Declaration of Conformity</b>	<b>Test Certificates</b>	<b>other</b>
---------------------------------	----------------------------------	--------------------------	--------------



[other](#)

[Environmental Confirmations](#)

[other](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**  
<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8WA18227EF18>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/8WA18227EF18/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8WA18227EF18](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WA18227EF18)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

**last modified:**

11.03.2015