

## swivel hoist ring, quality class 10

Screwed attachment point with ball bearing

CARTEC

### Application:

Screw-on, rotating attachment point for lifting heavy loads that need to be rotated or turned. Suitable for safe lifting in accordance with Machinery Directive 2006/42/EC.

### Execution:

- quality class 10 - compact, lightweight design, with DGUV certification
- with ball bearing for easier loading, loadable in all directions
- Can be rotated through 360°, swivel range of bracket max. 180°
- salmon, powder-coated surface
- permanent rotation under full load not permitted

### Advantage:

- 4-way safety in every load direction
- constructed, tested and certified according to GS-OA 15-04 - EN 1677



<b>Art. no.</b>	<b>77236 116</b>
<b>Brand</b>	CARTEC
<b>Manufacturer Part Number</b>	C800X0141620
<b>Thread dimension</b>	M16
<b>Load-carrying capacity</b>	1.4 t
<b>Internal width</b>	30 mm
<b>Bracket diameter</b>	13 mm
<b>Interior height</b>	46 mm
<b>Width of support plate</b>	38 mm
<b>Distance between lower edge of retainer holder and screw head</b>	50 mm
<b>Distance between lower edge of retainer holder and retainer</b>	105 mm
<b>Usable thread length</b>	20 mm
<b>Width across flats</b>	30 mm
<b>Gross Weight</b>	0.525 kg
<b>Product Group</b>	775

### EAN

8013429800702