



**FRONTLINE**  
Safety

---

**DATA SHEET**

---

Unit F, 230 Parkway Point, Springhill Parkway,  
Glasgow Business Park, Glasgow, UK, G69 6GA

[www.frontline-safety.co.uk](http://www.frontline-safety.co.uk)

**t:** +44(0)141 771 7749

**e:** [sales@frontline-safety.co.uk](mailto:sales@frontline-safety.co.uk)

# HONEYWELL BW™ FLEX SERIES MULTI-GAS DETECTOR

Whether you're protecting workers or first responders — in industries from steel and wastewater to paper and pulp — Honeywell BW™ Flex delivers the flexibility you need. Choose from more than 15 sensors to simultaneously detect up to 4 gas hazards.

## REAL-TIME GAS READINGS AT A GLANCE

Honeywell BW™ Flex features a large high-resolution display with readings available in a wide range of languages. Vital safety information is conveyed clearly and effectively, enabling faster decision-making to protect lives in hazardous environments. Its innovative design, compact size and ease of use builds on the legacy of Honeywell BW™ gas detection products.

## INTELLIGENT SENSORS FOR INCREASED SAFETY & UPTIME

Honeywell BW™ Flex incorporates i-Series intelligent sensors which monitor sensor status and provide advanced predictive calibration, maintenance and end-of-life information in real-time. These advanced alerts help reduce the likelihood of failure and increase awareness so preventive action can be taken to avoid safety incidents and unexpected downtime.

## SIMPLIFIED GAS REPORTING AND ANALYSIS

Honeywell BW™ Flex can be paired with a smartphone easily via Bluetooth®. Download the Honeywell Safety Suite Device Configurator app for quick and precise device management, maintenance, reporting and analysis. Increase productivity by simplifying tasks like recording incidents and save time with one-click download for all instrument data.

## FEATURES AND BENEFITS



### RELIABLE

Two months of battery runtime on a 4.5-hour charge with our new low-powered IR LEL sensor. No daily charging, no unexpected downtime.



### COMPATIBLE

The Honeywell BW™ Flex Series is compatible with the IntelliDoX instrument management system and Honeywell Safety Suite using Bluetooth® for wireless configuration.



### ACCURATE

Low-power infrared LEL sensor is immune to silicone poisoning, which means accurate monitoring of combustibles.



### EASY TO MANAGE

The IntelliFlash™ green light indicates when the detector is in compliance and the amber light indicates the need for maintenance.



### RESPONSIVE

1series sensors respond to dangerous gas levels in seconds, even in harsh temperatures.



### EASY TO USE

Small, lightweight and wearable. One-button operation.



Gas detector for the gas hazards that workers face most often: Combustible gas (LEL), oxygen (O<sub>2</sub>), hydrogen sulfide (H<sub>2</sub>S), carbon monoxide (CO), sulfur dioxide (SO<sub>2</sub>) and more variants coming soon.

# Honeywell BW™ Flex Series Technical Specifications

Technical Specifications	
Size	108.2 mm x 61.5 mm x 43.2 mm (4.29 in x 2.44 in x 1.7 in) with Alligator Clip 108.2 mm x 61.5 mm x 37.8 mm (4.29 in x 2.44 in x 1.49 in) with Klick Fast Stud
Weight	With Catalytic LEL: 189 g (6.7 oz) with Alligator Clip, 173 g (6.1 oz) with Klick Fast Stud With IR LEL: 186 g (6.6 oz) with Alligator Clip, 170 g (6.0 oz) with Klick Fast Stud
Working Temperature	-40°C to 60°C (-40°F to 140°F) and -20°C to 60°C (-4°F to 140°F) with Catalytic LEL sensor
Working Humidity	5% to 95%
Ingress Protection	IP66, IP68
Alarms and Type	Visual, vibrating, audible (95 dB); Low, High, TWA, STEL, Negative Drift, Over Limit, Multi-alarm
Self-Test	Perform diagnostic of sensor, circuitry on activation; Activated detector automatically performs analog sensor diagnostic every 10 minutes, digital sensor diagnostic every second
Typical Battery Life	40 days @ 8 hours of use per day with IR LEL 15 hours with Catalytic LEL (with NDIR CH4 sensor)
Connected Worker	Bluetooth® Low Energy (BLE) – Ability to connect to Honeywell’s Safety Communicator App, Device Configurator App and Safety Suite Device Configurator Software
User Options	<ul style="list-style-type: none"> <li>• Change High, Low, TWA and STEL alarm set points</li> <li>• Latching alarms</li> <li>• Set Calibration and/or bump test reminders</li> <li>• Assign worker and location assignments</li> <li>• Always on</li> </ul> User options only available via Device Configurator and Safety Suite Device Configurator
Certifications and Approvals	ATEX, IEC Ex, contains FCCID, contains IC, CSA approval pending
Device Warranty	Three-year warranty for sensors and detector

Sensor Specifications			
Gas Name	Measuring Range	Resolution	Working Temperature
CO	0 to 2000 ppm	1 ppm	-40°C to 60°C (-40°F to 140°F)
H <sub>2</sub> S	0 to 200 ppm	1 ppm (can set to 0.1ppm)	-40°C to 60°C (-40°F to 140°F)
SO <sub>2</sub>	0 to 150 ppm	0.1 ppm	-20°C to 50°C (-4°F to 122°F) intermittent -40°C to 55°C (-40°F to 131°F)
O <sub>2</sub>	0 to 30% VOL	0.1% VOL	-40°C to 60°C (-40°F to 140°F)
NDIR-CH <sub>4</sub>	0 to 100% LEL	1% LEL	-40°C to 60°C (-40°F to 140°F)
Catalytic LEL	0 to 100% LEL	1% LEL	-20°C to 60°C (-4°F to 140°F)



Caution: The infrared LEL sensor used in Honeywell BW™ Flex cannot detect hydrogen and acetylene. For applications involving these combustible gases, please specify the catalytic type LEL sensor.

**Americas**

Honeywell Analytics  
Distribution Inc.  
Tel: +1 847 955 8200  
Toll free: +1 800 538 0363  
detectgas@honeywell.com  
gasdetection@honeywell.com

**Europe, Middle East, Africa**

Life Safety Distribution GmbH  
Toll-Free 00800 333 222 44  
Middle East +971 4 450 5800  
Middle East +971 4 450 5852  
(Portable Gas Detection)  
gasdetection@honeywell.com  
www.honeywellanalytics.com

**Asia Pacific**

Honeywell Analytics Asia Pacific  
Tel: +82 (0) 2 6909 0300  
India Tel: +91 124 4752700  
analytics.ap@honeywell.com

**Technical Services**

EMEA: HAexpert@honeywell.com  
US/CA: ha.us.service@honeywell.com  
AP: ha.ap.service@honeywell.com

Bluetooth is a trademark or registered trademark of  
Bluetooth SIG, Inc.

GAS\_BW\_Flex Series\_DS | Rev A | 01/21  
© 2021 Honeywell International Inc.

**THE  
FUTURE  
IS  
WHAT  
WE  
MAKE IT**

**Honeywell**

**Thank you for reading this data sheet.**

For pricing or for further information, please contact us  
at our UK Office, using the details below.

**Please note** — Product designs and specifications are subject  
to change without notice. The user is responsible for  
determining the suitability of this product.



Unit F, 230 Parkway Point, Springhill Parkway,  
Glasgow Business Park, Glasgow, UK, G69 6GA

[www.frontline-safety.co.uk](http://www.frontline-safety.co.uk)

**t:** +44(0)141 771 7749

**e:** [sales@frontline-safety.co.uk](mailto:sales@frontline-safety.co.uk)