


# SBY457



## Flow transmitter with integrated backflow prevention

SBY32HF010KG/US



### Product characteristics

Measuring range	[l/min]	8...200
-----------------	---------	---------

Process connection		Rp 1 1/2
--------------------	--	----------

### Application

Media	Liquids; water; glycol solutions; oils; coolants
-------	--

Medium temperature	[°C]	-10...100
--------------------	------	-----------

Pressure rating	[bar]	25
-----------------	-------	----

### Electrical data

Operating voltage	[V]	18...32 DC; (to SELV/PELV)
-------------------	-----	----------------------------

Current consumption	[mA]	< 35
---------------------	------	------

Protection class		III
------------------	--	-----

Reverse polarity protection		yes
-----------------------------	--	-----

### Outputs

Output signal		analogue signal
---------------	--	-----------------

Analogue current output	[mA]	4...20
-------------------------	------	--------

Max. load	[Ω]	500
-----------	-----	-----

Short-circuit protection		yes
--------------------------	--	-----

Overload protection		yes
---------------------	--	-----

### Measuring/setting range

Measuring range	[l/min]	8...200
-----------------	---------	---------

# SBY457



## Flow transmitter with integrated backflow prevention

SBY32HF010KG/US

Accuracy / deviations		
Repeatability [% of the final value]		1
Measuring error [% of the final value]		± 5
Response times		
Response time [s]		< 0.01
Operating conditions		
Ambient temperature [°C]		0...60
Storage temperature [°C]		-15...80
Protection		IP 65; IP 67
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF [years]		778
Mechanical data		
Weight [g]		1414.5
Materials	brass chemically nickel-plated; PP; stainless steel (1.4404 / 316L); aluminium anodised; PA	
Materials (wetted parts)	stainless steel (1.4401 / 316); brass; brass chemically nickel-plated; PP; PPS; O-ring: FKM	
Process connection	Rp 1 1/2	
Switching cycles mechanical	10 million	
Remarks		
Remarks	Recommendation Use 200 micron filtration All data refer to water (20 °C).	
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12		




# SBY457



## Flow transmitter with integrated backflow prevention

SBY32HF010KG/US

### Connection



colours to DIN EN 60947-5-2

Core colours :


BN = brown

BU = blue

WH = white

### Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity