

INDICATOR LIGHT, 16MM, ROUND, PLASTIC, RED,
LAMPHOLDER W2 X 4.6D, WITHOUT LAMP



Figure similar

Design of the product		Complete unit round
Enclosure:		
Number of control points		0
Actuator:		
Design of the operating mechanism		indicator light
Product expansion optional Light source		Yes
Color		
• of the actuating element		Red
Material of the actuating element		plastic
Type of unlocking device		without
Number of switching positions		2
Front ring:		
Product component front ring		No
Holder:		
Material of the holder		Plastic
Contact block/ lampholder:		
Mounting type		W2 x 4.6d without lamp
Number of lampholders		1
Number of switching elements		0
General technical data:		
Product function		
• positive opening		No
• EMERGENCY STOP function		No

Product component • Light source		No
Type of voltage • of the operating voltage		AC/DC
Vibration resistance • acc. to IEC 60068-2-6		20 ... 200 Hz: 5g
Protection class IP		IP65
Equipment marking • acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750 • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2		H P P
Operating voltage • Rated value	V	5 ... 60

Auxiliary circuit:

Number of NC contacts • for auxiliary contacts		0
Number of NO contacts • for auxiliary contacts		0
Number of CO contacts • for auxiliary contacts		0

Connections/ Terminals:

Type of electrical connection		tab terminals
--------------------------------------	--	---------------


Ambient conditions:

Ambient temperature • during operation	°C	-25 ... +60
• during storage	°C	-40 ... +80

Installation/ mounting/ dimensions:

Mounting type		front mounting
Shape of the installation opening		round
Mounting diameter	mm	16

Certificates/ approvals:

General Product Approval			Declaration of Conformity	Test Certificates	other
 CCC	 UL		 EG-Konf.	Special Test Certificate	Confirmation

other	
Environmental Confirmations	other

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB22046BC06>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB22046BC06/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB22046BC06&lang=en

last modified:

09.03.2015