

Han M23 12+PE Female-solder(termination)



Part number 09 15 112 2722

Specification Han M23 12+PE Female-solder(termination)

HARTING eCatalogue https://b2b.harting.com/09151122722

Identification

| Category | Inserts |
|----------|-----------------------------|
| Series | Han [®] M23 Signal |
| Element | Inserts |

Version

| Termination method | Solder termination |
|--------------------|--------------------|
| Gender | Female |
| Number of contacts | 11 |
| PE contact | Yes |

Technical characteristics

| Conductor cross-section | 1 mm² max. |
|-------------------------|----------------------|
| Rated current | 8 A |
| Rated voltage | 200 V |
| Rated impulse voltage | 2.5 kV |
| Pollution degree | 3 |
| Insulation resistance | > 10 ¹⁰ Ω |
| Limiting temperature | -40 +125 °C |
| Mating cycles | ≥500 |

Material properties

| Material (insert) | Polyamide |
|---------------------|--------------|
| Colour (insert) | Grey |
| Material (contacts) | Copper alloy |



Material properties

| Surface (contacts) | Gold plated |
|---|--|
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant with exemption |
| RoHS exemptions | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| UL / CSA UL 1977 ECBT2.E235076 | |
|--------------------------------|--|
| | |
| 02 1011 E0B12.E200010 | |

Commercial data

| Packaging size | 5 |
|--------------------------------|---|
| Net weight | 9.4 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| eCl@ss | 27440205 Contact insert for industrial connectors |