CT-MBS.22S



General Information

CT-MBS.22S **Extended Product Type:** Product ID: 1SVR730010R3200 EAN: 4016779851374

Catalog Description: CT-MBS.22S Time relay, multifunction 2c/o, 24-48VDC, 24-240VAC

The CT-MBS.22S is a multifunction electronic time relay from the CT-S timer range. It Long Description:

provides 10 timing functions with 10 time ranges from 0.05 s to 300 h. This time relay operates with a rated control supply voltage of 24 - 48 V DC / 24 - 240 V AC and has a 2 c/o (SPDT) output with contacts rated at 250 V / 4 A. A control input works with volt-free (floating) triggering. The CT-MBS.22S offers the possibility of connecting a remote potentiometer for the fine adjustment of the time delay. The second of the c/o contacts can be selected as an instantaneous contact. A sealable transparent cover for protection against unauthorized changes is available as accessory. The device offers screw connection

technology with double-chamber cage connection terminals.

Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Time Relays

Ordering

Minimum Order Quantity: 1 piece **Customs Tariff Number:** 85364900 EAN: 4016779851374

Container Information

Package Level 1 Width: 97 mm Package Level 1 Length: 30 mm Package Level 1 Height: 109 mm Package Level 1 Gross Weight: 0.162 kg Package Level 1 Units: 1 piece

Dimensions

Product Net Height: 85.6 mm **Product Net Depth:** 103.7 mm **Product Net Weight:** 0.14 kg **Product Net Width:** 22.5 mm

Technical

Time Range: 0.05 s - 300 h 24 ... 240 V AC Rated Control Supply Voltage (U_s):

24 ... 48 V DC

50 Hz Rated Frequency (f):

60 Hz

DC Hz

Output: 2 c/o (SPDT) contacts **Terminal Type:** Screw Terminals

Rated Operational Current AC-12

(l_e):

 (l_e) :

(230 V) 4 A

Rated Operational Current AC-15

(230 V) 3 A

Rated Operational Current DC-12

(24 V) 4 A

Rated Operational Current DC-13

(l_e):

(24 V) 2 A

Minimum Switching Capacity:

12 V 10 mA

Rated Impulse Withstand Voltage

(U_{imp}):

Input Circuit 4 kV

Rated Insulation Voltage (Ui):

Output Circuit 1 / Output Circuit 2 4 kV Input Circuit / Output Circuit 500 V Output Circuit 1 / Output Circuit 2 300 V

Degree of Protection: Housing IP50

Terminals IP20

Overvoltage Category: **Pollution Degree:**

Short-Circuit Protective Devices:

Output Circuit NC - F Type Fuses 6 A

Output Circuit NO - F Type Fuses 10 A

AC-12 100000 cycle **Electrical Durability: Mechanical Durability:** 30000000 cycle

Connecting Capacity: Flexible with Ferrule 1x 0.5 ... 2.5 mm²

Flexible with Ferrule 2x 0.5 ... 1.5 mm²

Flexible with Insulated Ferrule 1x 0.5 ... 2.5 mm² Flexible with Insulated Ferrule 2x 0.5 ... 1.5 mm²

Flexible 1x 0.5 ... 2.5 mm² Flexible 2x 0.5 ... 1.5 mm² Rigid 1x 0.5 ... 4 mm² Rigid 2x 0.5 ... 2.5 mm²

Tightening Torque: 0.6 ... 0.8 N·m

8 mm Wire Stripping Length: **Mounting Position:** Any

Mounting on DIN Rail: TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715

Standards: IEC/EN 61812-1

UL 508

CAN/CSA C22.2 No.14

Timer Relay Type: **ON-Delay**

OFF - Delay Impulse - ON Impulse - OFF

Flasher with Reset, Starting with ON Flasher with Reset, Starting with OFF

Pulse Former ON / OFF Function

Symmetrical ON - and OFF - Delay Flasher Starting with ON or OFF Accumulative ON - Delay

Star-Delta

Environmental

RoHS Status: Following EU Directive 2011/65/EC

Ambient Air Temperature: Operation -25 ... +60 °C

Storage -40 ... +85 °C

Technical UL/CSA

Contact Rating UL/CSA: B300

Flexible 1x 18-14 AWG Connecting Capacity UL/CSA:

Flexible 2x 18-16 AWG Rigid 1x 20-12 AWG Rigid 2x 20-14 AWG

Tightening Torque UL/CSA: 7.08 in·lb

Maximum Operating Voltage

UL/CSA:

Output Circuit 300 V AC

Certificates and Declarations (Document Number)

1SVC730010M0000 Instructions and Manuals: **CB Certificate:** CB DK-5903-M1 **CCC Certificate:** CCC_2007010303255979 cULus Certificate: cULus508_20110711-E140448A

Data Sheet, Technical Information: 2CDC111120D0201 **Declaration of Conformity - CE:** 1SVD981008-0000

EAC Certificate: EAC_RU_C-DE.ME77.B.02016

GL Certificate: GL 36671-11HH

GOST Certificate: GOST_POCC_DE.AB76.D02256

RMRS Certificate: RMRS_12.04010.250 **RoHS Information:** 1SVD981001-4400

Classifications

E-nummer:	4033144
ETIM 4:	EC001439 - Timer relay
ETIM 5:	EC001439 - Timer relay
ETIM 6:	EC001439 - Timer relay
eClass:	7.0 27371790
Object Classification Code:	K

