

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1724530412](#)
Status: **Active**
Overview: EXTreme Ten60Power™ High-Current Connector
Description: EXTreme Ten60Power™ Wire-to-Board Right Angle Plug Assembly, 2 Power Circuit, 12 Signal Circuits, 2 Power Circuit

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980


General

Product Family PCB Headers
 Series [172453](#)
 Application Power, Signal, Wire-to-Board
 Overview [EXTreme Ten60Power™ High-Current Connector](#)
 Product Literature Order No 987650-1981
 Product Name EXTreme Ten60Power™
 UPC 889056069502

Physical

(p)ower-(s)ignal Configuration 2p - 12s - 2p
 Breakaway No
 Circuits (Loaded) 16
 Circuits (maximum) 16
 Color - Resin Black
 Durability (mating cycles max) 200
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Metal Copper Alloy
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin Liquid Crystal Polymer
 Net Weight 17.088/g
 Number of Rows 1, 3
 Orientation Right Angle
 PC Tail Length 2.84mm
 PCB Retention Yes
 Packaging Type Tray
 Pitch - Mating Interface 2.54mm, 7.50mm
 Plating min - Mating 0.762µm
 Plating min - Termination 2.540µm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Shrouded No
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style Through Hole

Electrical



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[172453](#) Series

Mates With

EXTreme Ten60Power™ Receptacle Housing [172510](#)

Current - Maximum per Contact
Voltage - Maximum

50.0A
600V AC / 250V DC

Material Info

Reference - Drawing Numbers
Sales Drawing

SD-172453-0412

This document was generated on 02/23/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION